ZVL-Dimension_2/18_C

Article number: 11214038

overview

- Carl Zeiss lens
- 18 mm
- F 2,0-22
- format 4/3"
- M.O.D. 0,090 m
- locating screw for aperture and focus
- C-mount



technical data

general data	
manufacturer	Carl Zeiss
mechanical data	
lens mount	C-mount
dimensions	57 mm × 66 mm
max. outer diameter	57 mm (without knurled screws) 63 mm (with knurled screws)
max. length (excl. thread)	66 mm
weight	≤ 291 g
filter thread	M 43,0 × 0,75

lens data	
lens resolution	20 MP
focal length	18 mm
focal range	≥ 12 mm … < 25 mm
format	4/3″
aperture	F2,0-22
aperture control	manual
M.O.D.	0,09 m
environmental conditions	
operating temperature	-22 … +55 °C

2020-01-27 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.