ZVL-LM12FC

Article number: 11700791

overview

- Kowa lens
- 12 mm
- F 1,8-16
- format 1,1"
- M.O.D. 0,1 m
- C-mount



technical data

general data	
manufacturer	Kowa
mechanical data	
lens mount	C-mount
dimensions	51 mm × 79,8 mm
max. outer diameter	51 mm (without knurled screws) 52 mm (with knurled screws)
max. length (excl. thread)	73,8 mm
weight	≤ 260 g
filter thread	M 49 × 0,75
lens data	
lens resolution	12 MP
focal length	12 mm

lens data	
focal range	≥ 12 mm … < 25 mm
format	1,1″
aperture	F1,8-16
aperture control	manual
M.O.D.	0,1 m
horizontal angle of view	60,0 °
vertical angle of view	46,9 °
diagonal angle of view	71,0 °
at image format	10,6 × 14,1 mm
environmental conditions	
operating temperature	-10 … +50 °C

2020-01-27 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.