Baumer
Passion for Sensors

Lenses / Lens accessories

ZVL-FL-CC1214A-2M

Article number: 11150226

overview

- Ricoh Imaging lens
- 12 mm
- F 1,4-16
- format 2/3"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



technical data

general data	
manufacturer	Ricoh Imaging
mechanical data	
lens mount	C-mount
dimensions	29,5 mm × 45,7 mm
max. outer diameter	29,5 mm (without knurled screws) 39,5 mm (with knurled screws)
max. length (excl. thread)	45,7 mm
weight	≤ 72 g

lens data	
lens resolution	2 MP
focal length	12 mm
format	2/3″
aperture	F1,4-16
aperture control	manual
M.O.D.	0,1 m

2020-01-27 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.