Power supply

Power Supply DIN Rail 24V/60W

Article number: 11088833

overview

- industrial DIN rail power supply 24V/60W
- for TX, VisiLine, VisiLine IP, MXG, SX and HX cameras (except HXC13)



technical data

electrical data	
input	screw clamp
input voltage	85 VAC .. 264 VAC
frequency	47 Hz .. 63 Hz
output	screw clamp (2 outputs)
operating voltage	24 VDC
current	2,5 A
ripple	150 mV p-p
level of efficiency	Level V

electrical data	
max. performance	60 W
mechanical data	
dimensions	40,0 mm × 90,0 mm × 100,0 mm
weight	≤ 330 g
material	plastic
environmental conditions	
operating temperature	0 … +40 °C
storage temperature	-20 … +85 °C
humidity	8 … 90 % (non-condensing)

2020-01-30 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.