Power supply

Power Supply 24V/1.0A Int. DC Connector

Article number: 11079750

overview

- power supply 24V/1,0A with adapters for EU, US, UK AU, KR
- for VCXG.I(.XT), VLXT and VeriSens



technical data

electrical data	
input	adapter: EU, US, UK, AU, KR (changeable)
input voltage	90 VAC .. 264 VAC
frequency	47 Hz .. 63 Hz
output	DC Plug 5,5 x 2,1 mm
operating voltage	24 VDC
current	1 A
tolerance	5 %
ripple	240 mV p-p
level of efficiency	Level V

electrical data	
max. performance	24 W
mechanical data	
dimensions	93,5 mm × 46,0 mm × 36,2 mm
cable length [m]	5 m
weight	≤ 170 g
material	plastic
environmental conditions	
operating temperature	0 … +40 °C
storage temperature	-20 … +85 °C
humidity	8 … 90 % (non-condensing)

2020-01-30 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.