Baumer
Passion for Sensors

Cables


KSG 34A/KSG45AP1000G/E

Ethernet cable, 10,0 m

Article number: 11051929

overview

- shielded Ethernet cable
- straight M12/4-pin male connector to RJ45
- length 10,0 m



technical data

electrical data	
number of poles	4
connectors	M12 male connector, screw lock RJ45
mechanical data	
bending radius static	26 mm
bending radius moved in-stallation	52 mm
use in cable carriers	no
cable length [m]	10 m
weight	≤ 575 g

mechanical data	
material	PUR
interface	
data interface	Ethernet
environmental conditions	
flame resistance	DIN EN 60332-1-2
halogen-free	IEC 60754-1
resistance to oil	DIN EN 60811-2-1
operation temperature (static)	-20 … +80 °C
protection class	IP 65/67 (camera side)

2020-02-05 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.


Cables

KSG 34A/KSG45AP1000G/E

Ethernet cable, 10,0 m

Article number: 11051929

pin assignment



M12	RJ45
1:	1
3:	2
2:	3
4:	6

2020-02-05 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.