Obj LINOS MeVis C 16mm/f1,6

Article number: 11051403

overview

- Linos lens
- 16 mm
- F 1,6-16
- format 2/3"
- M.O.D. 0,15 m
- C-mount
- Phase-Out starting 08/20, alternative via sales



technical data

general data	
manufacturer	Linos
mechanical data	
lens mount	C-mount
dimensions	42 mm × 51,5 mm
max. outer diameter	42 mm (without knurled screws) 52 mm (with knurled screws)
max. length (excl. thread)	51,5 mm
weight	≤ 170 g
filter thread	M 35,5 × 0,5

lens data	
lens resolution	9 MP
focal length	16 mm
focal range	≥ 12 mm … < 25 mm
format	2/3″
aperture	F1,6-16
aperture control	manual
M.O.D.	0,15 m

2020-08-11 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.