Cables


Z-KSG 32FP0500G

Shielded cable 8 wires, male connector, 5,0 m

Article number: 11118799

overview

- shielded process interface cable
- M8/8-pin male connector to open wires
- cable carrier compatible
- length 5,0 m
- Phase-Out starting 08/20, alternative via sales



technical data

electrical data	
shielding	yes
number of poles	8
connectors	M8 male connector, screw lock
mechanical data	
smallest bending radius static	29,5 mm
smallest bending radius moved installation	59 mm
bending cycles	2000000
use in cable carriers	yes
cable length [m]	5 m
weight	≤ 246 g
material	PUR, halogen-free

interface	
data interface	process interface
environmental conditions	
flame resistance	DIN EN 60332-1-2 VDE 0482-332-1-2 IEC 60332-1-2 CSA FT-2
halogen-free	DIN EN 50267-2-1 IEC 60754-1 VDE 0482-267-2-1
resistance to oil	DIN EN 60811-2-1, 168 h at 100°C
operation temperature (static)	-50 ... +80 °C
protection class	IP 65/67 (camera side)

2020-08-11 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.


Cables

Z-KSG 32FP0500G

Shielded cable 8 wires, male connector, 5,0 m

Article number: 11118799

pin assignment



M8	color	M8	color
1:	WH	5:	GY
2:	BN	6:	PK
3:	GN	7:	BU
4:	YE	8:	RD

2020-08-11 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.