


# FSE 200D2Y00

Plastic fiber optic cable

Article number: 10135346

## Overview

- Through-beam type
- Actual range up to 506 mm
- Cylindrical smooth sensing head  $\varnothing 1.5$  mm
- Bend-tolerant plastic fiber 200 cm long, suitable for flexible cable carriers
- Operating temperature up to +70 °C
- For compact fiber optic sensors FVDK 10 and OF10



Picture similar

## Technical data

### General data

Operating principle	Through-beam type
Actual range Sb	506 mm
Fiber optic head	Cylindrical smooth
Operating temperature	-30 ... +70 °C
Exit angle	60°
Fiber optics can be shortened to length	Yes
Integrated lens	No
Adaptable lens	No
Infrared light compatibility (1450 nm)	No


### General data

Smallest object recognizable	0.01 mm
------------------------------	---------

### Mechanical data

Width / diameter (head)	1.5 mm
Height / length (head)	15 mm
Material (head)	Stainless steel
Bending radius (fixed)	4 mm
Cable jacket diameter	1 mm
Material cable jacket	PE
Material (fiber optic cable)	Plastic
Length (fiber optic cable)	200 cm

## Dimension drawing



## Actual range diagram

	Mode	Actual Range Sb [mm]
OF10	Ultra-High-Speed	144
	High-Speed	194
	Standard	208
	High-Resolution	300
	Long-Range	379
	Ultra-Long-Range	506
FVDK 10x6	Fast	154
	Semi Fast	246
	Normal	290
FVDK 10x5	Potentiometer	47

**Accessories**
**Fitting fiber optic sensors**

11252204	OF10.FR-GW2J.B2NV/A014
11244386	OF10.FR-GW2J.B2CV/A014
11224111	OF10.FR-PW1B.B2N
11224008	OF10.FR-NW1B.B2CV
11224009	OF10.FR-NW1B.B2N
11224110	OF10.FR-PW1B.B2CV
11244384	OF10.FR-GW2J.B2N/A014
10162867	FVDK 10N5101
10162865	FVDK 10N5101/S35A
10162866	FVDK 10P5101
10162864	FVDK 10P5101/S35A
11045446	FVDK 10N66Y0
11045448	FVDK 10N66Y0/S35A
11045460	FVDK 10N66YR
11045445	FVDK 10P66Y0
11045447	FVDK 10P66Y0/S35A
11045449	FVDK 10P66YR
11214490	FVDK 10P66ZR
11214493	FVDK 10P66Z0/S35A
11214478	FVDK 10P66Z0
11214492	FVDK 10N66ZR
11214494	FVDK 10N66Z0/S35A
11214479	FVDK 10N66Z0
11045462	FVDK 10N66YM
11045464	FVDK 10N66YS
11045461	FVDK 10P66YM
11045463	FVDK 10P66YS

**Mounting accessories**

10114652	Cutting tool for plastic fiber optics
10119912	Mounting bracket Ø 1,1 mm

**Lenses and components**

10140260	Reduction tube
----------	----------------