

ESW 33JP0500GS

90° shielded cable 12 wires, female connector, 5,0 m

Article number: 11195094

Overview

- shielded process interface cable
- 90° angled M12/12-pin female connector to open wires
- cable carrier compatible
- suitable for robotic applications (+/- 180°/m, min. 500.000 torsion cycles)
- length 5,0 m



Picture similar

Technical data

Electrical data

Shielding	yes
Number of poles	12
Connectors	M12 female connector, angled, screw lock open wires
Suitable for operation with max 60 V (nominal 48 V)	yes
Suitable for operation with max 60 V (nominal 48 V) (info)	The M12 connectors must comply with the IEC 61076-2-101 standard. The dielectric strength and withstand voltage for the plug/socket combination must be checked according to DIN EN 60664-1:2008-01 for 60 V.

Mechanical data

Smallest bending radius static	30 mm
Smallest bending radius moved installation	72 mm

Mechanical data

Bending cycles	1000000
Use in cable carriers	yes
Cable length [m]	5 m
Material	PUR, halogen-free

Interface

Data interface	Process interface
----------------	-------------------

Environmental conditions


Flame resistance	IEC 60332-2-2
Halogen-free	DIN EN 50267-2-1
Operation temperature (static)	-40 ... +90 °C
Operation temperature (moved installation)	-25 ... +60 °C
Conformity	UL RoHS
Protection class	IP 65/67/68 (mounted)

ESW 33JP0500GS


90° shielded cable 12 wires, female connector, 5,0 m

Article number: 11195094

Dimension drawing



Pin assignment



M12	color	M12	color
1:	BN	7:	BK
3:	WH	10:	VT
6:	YE	9:	RD
4:	GN	2:	BU
5:	PK	11:	GYPK
8:	GY	12:	RDBU