

Diffuse contrast sensors

OZDK 14P1901/S14



| general data | |
|-----------------------------------|--------------------------|
| type | diffuse contrast sensor |
| light source | pulsed red laser diode |
| sensing distance Tw | 20 300 mm |
| optimum operating distance | 40 60 mm |
| repeat accuracy | < 0,2 mm at laser focus |
| alignment / soiled lens indicator | flashing light indicator |
| power on indication | LED green |
| light indicator | LED yellow |
| sensitivity adjustment | Teach-in |
| laser class | 2 |
| distance to focus | 115 mm |
| wave length | 650 nm |
| | |



| mechanical data | |
|------------------|---------------------|
| width / diameter | 14,8 mm |
| height / length | 43 mm |
| depth | 31 mm |
| type | rectangular |
| housing material | plastic (ASA, MABS) |
| front (optics) | PMMA |
| connection types | connector M12 4 pin |
| | |

| ambient conditions | | |
|-----------------------|------------|--|
| operating temperature | -10 +50 °C | |
| protection class | IP 67 | |



