


电感式接近开关

IR12.P10S-11148588

尺寸图



基本参数

安装类型	非屏蔽
特殊型号	增强距离 (GammaProx)
额定感应距离 S_n	10 mm
温漂	$\pm 10\%$ (0 ... +60 °C) $\pm 15\%$ (-25 ... +75 °C)
磁滞	3 ... 20 % (Sr)
输出指示灯	LED 红色
修正系数典型值	软钢 100 %, 不锈钢 75 %, 铝 50 %

电气参数

开关频率	< 1,5 kHz
工作电压范围 +Vs	6 ... 36 VDC
电流消耗 (最大) (无负载)	10 mA
输出电路	PNP 常闭 (NC)
压降 V_d	< 2 VDC
输出电流	< 100 mA
短路保护	是
反向极性保护	是

机械参数

类型	圆柱型 螺纹版
材料 (感应面)	PBT
外壳材料	黄铜镍电镀
尺寸	12 mm
外壳长度	50 mm
连接器类型	电缆, 2 m
旋紧力矩 max.	15 Nm (A: 10 Nm)


环境条件

操作温度	-25 ... +75 °C
防护等级	IP 67

照片



连接图




- 增强感应距离


电感式接近开关

IR12.P10S-11148588


不同安装情况的修正系数 (近似值)



Mounting material	Correction factor
Mild steel	100 %
Stainless steel	100 %
Aluminum	100 %



Mounting material	Correction factor
Mild steel	105 %
Stainless steel	100 %
Aluminum	100 %



Mounting material	Correction factor
Mild steel	not possible
Stainless steel	not possible
Aluminum	90 %

mounting instructions

