
Through beam sensors

OR18.EL-11157818



general data	
type	through beam sensor
emitter / receiver	receiver
actual range Sb	55 m
nominal range Sn	60 m
output indicator	LED yellow
power on indication	LED green
sensitivity adjustment	potentiometer, 270°

electrical data	
response time / release time	< 0,34 ms
voltage supply range +Vs	10 30 VDC
current consumption max. (no load)	45 mA
current consumption typ.	35 mA
voltage drop Vd	< 2 VDC
output function	light / dark operate
output circuit	PNP complementary
output current	< 100 mA
short circuit protection	yes
reverse polarity protection	yes

mechanical data	
width / diameter	18 mm
height / length	77 mm
type	cylindrical threaded
housing material	brass nickel plated
front (optics)	PMMA
connection types	cable 4 pin, 2 m

ambient conditions	
operating temperature	-10 +55 °C
protection class	IP 67



