




Edge sensors**OXE7.E25T-11111452****dimension drawing****general data**

| | |
|----------------------------------|---|
| type | measuring mode: edges, center, width, gap |
| version | PosCon OXE7 |
| measuring range (width) | 75 ... 125 mm |
| measuring range (distance) | 150 ... 250 mm |
| measuring frequency | 125 ... 500 Hz |
| resolution | 30 ... 50 µm |
| repeat accuracy | ± 10 µm |
| smallest detectable object width | 1,5 mm |
| smallest detectable gap | 2 mm |
| smallest detectable step | 2 mm |
| linearity error | ± 80 ... ± 120 µm |
| temperature drift | < 0,05 % measured value/K |
| power on indication | LED green |
| output indicator | LED yellow / LED red |
| light source | pulsed red laser diode |
| wave length | 656 nm |
| laser class | 1 |
| optical peak power max. | 3 mW |
| adjustment | Touch Display, RS485 |

photo**connection diagram****electrical data**

| | |
|------------------------------------|----------------------------|
| response time / release time | 4 ... 16 ms |
| voltage supply range +Vs | 15 ... 28 VDC |
| current consumption max. (no load) | 150 mA |
| output circuit | analog and RS 485 |
| output signal | 4 ... 20 mA / 0 ... 10 VDC |
| switching output | push-pull |
| output function | Out 1 / Alarm |
| output current | < 100 mA |
| baud rate | 115200, adjustable |
| reverse polarity protection | yes, Vs to GND |
| short circuit protection | yes |

alignment of the laser line

Edge sensors**OXE7.E25T-11111452****mechanical data**

| | |
|------------------|-------------------------|
| width / diameter | 26 mm |
| height / length | 74 mm |
| depth | 55 mm |
| type | rectangular, front view |
| housing material | aluminum |
| front (optics) | glass |
| connection types | connector M12 8 pin |
| weight | 130 g |

laser warning**CLASS 1 LASER PRODUCT**

IEC 60825-1/2014
Complies with 21 CFR 1040.10 and 1040.11
except for deviations pursuant to laser
notice No. 50, dated June 24, 2007

**ambient conditions**

| | |
|-------------------------|--|
| ambient light immunity | < 25 kLux |
| operating temperature | -20 ... +50 °C |
| protection class | IP 67 |
| storage temperature | -25 ... +75 °C |
| vibration (sinusoidal) | IEC 60068-2-6:2008 1.5 mm p-p at f = 10 - 57 Hz, 10 cycles per axis 10 g at f = 58 - 2000 Hz, 10 cycles per axis |
| shock (semi-sinusoidal) | IEC 60068-2-27:2009 50 g / 11 ms resp. 100 g / 6 ms, 10 jolts per axis and direction 100 g / 2 ms, 5000 jolts per axis and direction |

- Conditions for the following characteristics:

- measuring frequency 1) 2)
- resolution 1) 3)
- repeat accuracy 1) 3)
- linearity error 1) 4)
- response time / release time 1) 2) 3)
- 1) Measurement with Baumer standardized measuring equipment and targets. Measuring on 90% reflectivity (white)
- 2) Depending on the size of the measuring field and OBJECT light/dark mode
- 3) Without filtering / no averaging
- 4) Measured symmetrically around the reference point with 50% of the measuring field