

# Inclination sensors

2-dimensional, measuring range up to  $\pm 60^\circ$

Analog

## GIM140R - 2-dimensional, analog



GIM140R

### Features

- Size 48 mm
- Interface Analog
- MEMS capacitive measuring principle
- Measuring range 2-dimensional: up to  $\pm 60^\circ$
- Aluminium housing
- Protection IP 67/IP 69K
- Connection cable
- Teach input for adjustment of zero position

### Optional

- Analog output with out-of-range diagnostic

### Technical data - electrical ratings

Voltage supply	8...30 VDC 12...30 VDC
Reverse polarity protection	Yes
Short-circuit proof	Yes
Consumption typ.	8 mA (24 VDC, w/o load, voltage output) 12 mA (w/o load, current output)
Interface	Analog (4...20 mA / 0.5...4.5 V / 0...10 V)
Load resistor	Between Out/0 V $\geq 3 \text{ k}\Omega$ / voltage output 270 $\Omega$ at 10 VDC (500 $\Omega$ at 15 VDC) / current output
Measuring range	$\pm 10^\circ/\pm 30^\circ/\pm 45^\circ/\pm 60^\circ$
Resolution	0.05 °
Accuracy (+25 °C)	$\pm 0.4^\circ$
Sensing method	MEMS technology
Interference immunity	DIN EN 61000-6-2
Emitted interference	DIN EN 61000-6-3
Programmable parameters	Preset
Diagnostic function	Out-of-range diagnostics

### Technical data - mechanical design

Dimensions W x H x L	48 x 14 x 45 mm
Protection DIN EN 60529	IP 67/IP 69K
Material	Housing: aluminium, anodised
Corrosion protection	ISO 9227:2017 salt mist according to ISO 12944-6:1998 C5-M (CX)
Operating temperature	-40...+85 °C
Resistance	DIN EN 60068-2-6 Vibration 10 g, 10-2000 Hz DIN EN 60068-2-27 Shock 50 g, 11 ms
Weight approx.	50 g
Connection	Cable 0.3 m, radial

**Inclination sensors**  
**2-dimensional, measuring range up to  $\pm 60^\circ$**   
**Analog**

**GIM140R - 2-dimensional, analog**

**Part number**

GIM140R- **M** **2** . **K** .**A**

Option

Without option

/4822 Output signal with out-of-range diagnostics

Voltage supply / interface

V3 8...30 VDC / Analog 0.5...4.5 VDC

V6 12...30 VDC / Analog 0...10 VDC

C0 12...30 VDC / Analog 4...20 mA

Connection

K Cable 0.3 m, Standard 5x0.5 mm<sup>2</sup>

Measuring range

10  $\pm 10^\circ$

45  $\pm 45^\circ$

30  $\pm 30^\circ$

60  $\pm 60^\circ$

Number of axes

2 2-dimensional

Housing

M Metal

# Inclination sensors

2-dimensional, measuring range up to  $\pm 60^\circ$

Analog

## GIM140R - 2-dimensional, analog

### Installation position



The 2-dimensional inclination sensor must be mounted with the base plate in horizontal position, i.e. parallel to the horizontal line. The sensor can be inclined both towards the X and Y axis at the same time. For each axis a separate measured value is provided.

Default on delivery the inclination sensor will apply the selected sensing range to both axis, for example  $\pm 30^\circ$  with the zero passage being precisely in the horizontal line.

$Y = 0^\circ$



$Y = -30^\circ$



$X = 0^\circ$



$X = +30^\circ$



### Terminal assignment

Cable

Core color	Signal	Description
White	0 V	Ground relating to +Vs
Brown	+Vs	Voltage supply
Green	Out_X	Output
Yellow	Out_Y	Output
Grey	Teach	Teach-input

Cable data: 5 x 0.5 mm<sup>2</sup>

### Teach process

The teach-in function enables rapid and easy commissioning in the field.

#### Setting zero

- Get inclination sensor on position intended for zero position.
- Set teach input for  $5 < t < 10$  seconds on high level.

### Trigger level

#### Teach-input

High level	>2.1 V
Low level	<1 V
Maximum	+Vs

# Inclination sensors

## 2-dimensional, measuring range up to $\pm 60^\circ$


### Analog

#### GIM140R - 2-dimensional, analog


##### Output signals

Analog output


Measuring range  $-30 \dots +30^\circ$



Measuring range  $-45 \dots +45^\circ$



Measuring range  $-60 \dots +60^\circ$



# Inclination sensors

2-dimensional, measuring range up to  $\pm 60^\circ$


Analog

## GIM140R - 2-dimensional, analog


### Output signals

Analog output with out-of-range diagnostic


Measuring range  $-30 \dots +30^\circ$



Measuring range  $-45 \dots +45^\circ$



Measuring range  $-60 \dots +60^\circ$



**Inclination sensors**  
2-dimensional, measuring range up to  $\pm 60^\circ$   
Analog

**GIM140R - 2-dimensional, analog**

**Dimensions**

