19/11/2018 Subject to modification in technic and design. Errors and omissions excepted.

Totalizers mechanic

Revolution counter

Display 5 digits, manual reset (zero) by lever

U 410



U 410 - Revolution counter

Technical data - mechanical design	
Function	Revolution counter
Display	White numbers on black
Number of digits	5-digits
Digit height	7 mm
Zero setting	Manual by reset lever. Do not let snap or make jerky movements.
Count mode	Adding in a rotational direction to be indicated, subtracting in reverse direction. 1 rev. = 1 count
Drive shaft	Both sides, ø7 mm
Operating speed	≤3000 rpm
Measuring range	99 999
Ambient temperature	0+60 °C
Housing type	Surface mount housing with mounting plate
Housing colour	Grey
Dimensions W x H x L	106 x 64 x 45 mm
Dimensions mounting plate	e 120 x 64 mm
Mounting type	Base plate, 4 long mounting holes
Weight approx.	380 g
Materials	Housing: Hostaform POM, grey Base blate: steel zinc-coated

Features

- Revolution counter
- Adding
- Display 5-digits
- Reset by lever

Totalizers mechanic

Revolution counter


Display 5 digits, manual reset (zero) by lever

U 410

Part number U 410. 010 Display / direction of rotation 5 digits 99 999 / I 5 digits 99 999 / II Count mode / drive 1 revolution = 1 digit / drive shaft on both sides 1 revolution = 10 digits / drive shaft on both sides Housing Surface mount housing, grey Zero setting 010 With reset lever

Direction of strokes and rotation







Towards user Direction of rotation or stroke direction II

Dimensions

