Baumer
Passion for Sensors

CX series

VCXG-32C

Gigabit Ethernet, 3,1 Megapixel, Color

Article number: 11165950

overview

- 2048 × 1536 px
- Sony IMX265
- 1/1.8″ CMOS
- 39 fps
- Gigabit Ethernet
- available



technical data

sensor information	
sensor	Sony IMX265
resolution	2048 × 1536 px
exposure time	0,001 … 60000 ms
pixel size	3.45 × 3.45 µm
shutter type	Global shutter
sensor type	1/1.8″ CMOS
acquisition formats	
image formats, interface frame rate max.	Full Frame, 2048 × 1536 px, max. 39 fps Binning 2×2, 1024 × 768 px, max. 55 fps Binning 2×1, 1024 × 1536 px, max. 55 fps Binning 1×2, 2048 × 768 px, max. 55 fps
image formats, aquisition frame rate max. (Burst Mode)	Full Frame, 2048 × 1536 px, max. 55 fps
pixel formats	BayerRG8 BayerRG10 BayerRG12 BayerRG12 Packed Mono8 Mono10 Mono12 Mono12 Packed RGB8 BGR8
image preprocessing	
analog controls	Gain (0 … 48 dB) Offset (0 … 255 LSB 12 Bit)

image preprocessing	
color models	Mono Raw Bayer RGB
camera features	
synchronization	free running trigger
trigger sources	Hardware software ActionCommand
trigger delay	0 … 2 sec, tracking and buffering of up to 256 trigger signals
internal image buffer	72 MB 8 images (Trigger Mode) 1 image (Free Running Mode)
interfaces and connectors	
data interface	Gigabit Ethernet, Transfer rate 1000 Mbits/sec, Fast Ethernet, Transfer Rate 100 Mbits/sec, Connector: 8P8C Modular Jack (RJ45), screwable type
process interface	M8 / 8 pins (SACC-DSI-M8MS-8CON-M8-L180)
power supply	M8 / 8 pins or PoE
mechanical data	
lens mount	C-mount
width	29 mm
height	29 mm
depth	49 mm

2019-11-27 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.

CX series

VCXG-32C

Gigabit Ethernet, 3,1 Megapixel, Color


Article number: 11165950

technical data

mechanical data	
weight	≤ 120 g
material	zinc die casting, nickel-plated, IP 40
electrical data	
voltage supply range +Vs	12 … 24 V DC (external power supply) 36 … 57 V DC (Power over Ethernet)
power consumption	approx. 2,6 W @ 12 VDC and 39,5 fps approx. 3,2 W @ 48 VDC (PoE) and 39,5 fps
non-volatile memory	
flash memory size	128 kB
environmental conditions	
operating temperature	+5 … +65 °C @ T = measurement point

environmental conditions	
humidity	10 … 90 % (non-condensing)
protection class	IP 40
digital I/Os	
lines	1 input line 1 output line 2 general purpose lines
conformity	
conformity	CE RoHS KC (MISP-REI-BkR-VCXG-51C) EAC

dimension drawing



The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.
2019-11-27