

overview

- 1920 × 1200 px
- ON Semiconductor PYTHON2000
- 2/3" CMOS
- 41 fps
- Gigabit Ethernet
- available



technical data

sensor information

sensor	ON Semiconductor PYTHON2000
resolution	1920 × 1200 px
exposure time	0,04 ... 1000 ms
pixel size	4.8 × 4.8 µm
shutter type	Global shutter
sensor type	2/3" CMOS

acquisition formats

image formats, interface frame rate max.	Full Frame, 1920 × 1200 px, max. 41 fps Binning 2×2, 960 × 600 px, max. 41 fps Binning 2×1, 960 × 1200 px, max. 41 fps Binning 1×2, 1920 × 600 px, max. 41 fps
pixel formats	BayerRG8 BayerRG10

image preprocessing

analog controls	Gain (0 ... 12 dB) Offset (0 ... 63 LSB 10 Bit)
color models	Raw Bayer

camera features

synchronization	free running trigger
trigger sources	Hardware software
internal image buffer	7 MB 1 image (Trigger Mode) 1 image (Free Running Mode)

interfaces and connectors

data interface	Gigabit Ethernet, Transfer rate 1000 Mb/s/sec, Fast Ethernet, Transfer Rate 100 Mb/s/sec, Connector: 8P8C Modular Jack (RJ45), screwable type
process interface	M8 / 4 pins (SACC-DSI-M 8MS-4CON-L180)
power supply	M8 / 4 pins

mechanical data

lens mount	CS-mount
width	29 mm
height	29 mm
depth	49 mm
weight	≤ 120 g
material	zinc die casting, nickel-plated, IP 40

electrical data

voltage supply range +Vs	12 ... 24 V DC (external power supply)
power consumption	approx. 2,6 W @ 12 VDC and 41 fps

non-volatile memory

flash memory size	128 kB
-------------------	--------

environmental conditions

operating temperature	+5 ... +65 °C @ T = measurement point
humidity	10 ... 90 % (non-condensing)
protection class	IP 40

digital I/Os

lines	1 input line 1 output line
-------	-------------------------------

VEXG-25C

Gigabit Ethernet, 2,3 Megapixel, Color

Article number: 11166633

technical data

conformity

conformity
CE
RoHS
EAC

dimension drawing

