

overview

- 2048 × 1088 px
- ams (CMOSIS) CMV2000
- 2/3" CMOS
- 105 fps
- Dual Gigabit Ethernet
- available



technical data

sensor information

sensor	ams (CMOSIS) CMV2000
resolution	2048 × 1088 px
exposure time	0,02 ... 1000 ms
color filter	RGB Bayer Mosaic
pixel size	5.5 × 5.5 µm
shutter type	Global shutter
sensor type	2/3" CMOS

acquisition formats

image formats, interface frame rate max.	Full Frame, 2048 × 1088 px, max. 105 fps
image formats, aquisition frame rate max. (Burst Mode)	Full Frame, 2048 × 1088 px, max. 337 fps
pixel formats	BayerGB8 BayerGB10 BayerGB12

image preprocessing

analog controls	Gain (0 ... 12 dB) Offset (0 ... 255 LSB)
color models	Raw Bayer

camera features

synchronization	free running trigger
trigger sources	Hardware software ActionCommand
trigger delay	0 ... 2 sec, tracking and buffering of up to 512 trigger signals

camera features

sequencer	Automated control for series of images using different sets of parameters
sequencer parameter	exposure time gain factor output
digital inputs	3 input line (each with Debouncer)
digital outputs	3 output lines
internal image buffer	256 MB

interfaces and connectors

data interface	Dual Gigabit Ethernet, Transfer rate 2000 Mb/s/sec, Connector: 2 x 8P8C Modular Jack (RJ45), screwable type
process interface	M8 / 8 pins
power supply	M8 / 3 pins

mechanical data

lens mount	C-mount (F-mount on request)
width	52 mm
height	52 mm
depth	55 mm
weight	≤ 232 g
material	housing: aluminum

electrical data

voltage supply range +Vs	20 ... 30 V DC (external power supply) 38 ... 57 V DC (Power over Ethernet)
power consumption	approx. 7,7 W @ 24 VDC and 105,0 fps approx. 8,9 W @ 48 VDC (PoE) and 105,0 fps

technical data

environmental conditions

operating temperature	+5 ... +50 °C
humidity	10 ... 90 % (non-condensing)
protection class	IP 40

conformity

conformity	CE
	RoHS
	FCC
	EAC

dimension drawing

