


overview

- 5120 × 3840 px
- ams (CMOSIS) CMV20000
- 35 mm CMOS
- 16 fps
- Gigabit Ethernet
- available



technical data

sensor information

sensor	ams (CMOSIS) CMV20000
resolution	5120 × 3840 px
exposure time	0,19 ... 1000 ms
pixel size	6.4 × 6.4 µm
shutter type	Global shutter
sensor type	35 mm CMOS

acquisition formats

image formats, interface frame rate max.	Full Frame, 5120 × 3840 px, max. 6 fps
image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 5120 × 3840 px, max. 16 fps
pixel formats	Mono8 Mono12

image preprocessing

analog controls	Gain (0 ... 12 dB) Offset (0 ... 255 LSB 12 Bit)
color models	Mono
image processing	VisualApplets 2.x

camera features

synchronization	free running trigger
trigger sources	Hardware software ActionCommand
trigger delay	0 ... 2 sec, tracking and buffering of up to 512 trigger signals

camera features

sequencer	Automated control for series of images using different sets of parameters
sequencer parameter	exposure time gain factor ROI Offset x ROI Offset y
digital inputs	1 input line
digital outputs	3 output lines
internal image buffer	512 MB

interfaces and connectors

data interface	Gigabit Ethernet, Transfer rate 1000 Mbits/sec, Connector: 8P8C Modular Jack (RJ45), screwable type
process interface	M8 / 8 pins (2x)
power supply	M8 / 8 pins

mechanical data

lens mount	M58-mount (F-mount, M42, C-mount via adapter)
width	60 mm
height	60 mm
depth	54,25 mm
weight	≤ 290 g (M58-mount)
material	housing: aluminum

electrical data

voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
--------------------------	--

LXG-200M.P

Gigabit Ethernet, 20 Megapixel, Monochrome

Article number: 11155111

technical data

electrical data

power consumption	approx. 6,5 W @ 24 VDC
	approx. 6,5 W @ 48 VDC (PoE)

non-volatile memory

flash memory size	128 kB
-------------------	--------

environmental conditions

operating temperature	+5 ... +50 °C
-----------------------	---------------

environmental conditions

humidity	10 ... 90 % (non-condensing)
protection class	IP 40

conformity

conformity	CE
	RoHS
	EAC

dimension drawing

