

overview

- 1288 × 960 px
- Sony ICX445
- 1/3" CCD
- 42 fps
- Gigabit Ethernet
- Phase-Out starting 09/19, alternative via sales



technical data

sensor information

sensor	Sony ICX445
resolution	1288 × 960 px
exposure time	0,004 ... 60000 ms
pixel size	3.75 × 3.75 µm
shutter type	Global shutter
sensor type	1/3" CCD

acquisition formats

image formats, interface frame rate max.	Full Frame, 1288 × 960 px, max. 42 fps
pixel formats	Mono8 Mono12 Mono12 Packed

image preprocessing

analog controls	Gain (0 ... 29 dB) Offset (0 ... 1023 LSB 14 Bit)
color models	Mono

camera features

synchronization	free running trigger
trigger sources	Hardware software ActionCommand
trigger delay	0 ... 2 sec, tracking and buffering of up to 512 trigger signals
sequencer	Automated control for series of images using different sets of parameters

camera features

sequencer parameter	exposure time gain factor output line ROI Offset x ROI Offset y
digital inputs	1 input line
digital outputs	3 output lines
internal image buffer	120 MB

interfaces and connectors

data interface	Gigabit Ethernet, Transfer rate 1000 Mb/s/sec, Fast Ethernet, Transfer Rate 100 Mb/s/sec, Connector: 8P8C Modular Jack (RJ45), screwable type
process interface	SACC-DSI-M8FS-3CON-M10-L180 SH
power supply	SACC-DSI-M 8MS-6CON-L180 SH

mechanical data

lens mount	C-mount
width	33 mm
height	33 mm
depth	48 mm
weight	≤ 150 g
material	zinc die casting, nickel-plated, IP 40

electrical data

voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
power consumption	approx. 3,6 W @ 12 VDC and 42,0 fps approx. 3,8 W @ 48 VDC (PoE) and 42,0 fps

VLG-12M

Gigabit Ethernet, 1,2 Megapixel, Monochrome

Article number: 11099354

technical data

non-volatile memory

flash memory size 128 kB

environmental conditions

operating temperature +5 ... +50 °C

humidity 10 ... 90 % (non-condensing)

protection class IP 40

digital I/Os

lines 1 input line
3 output lines

conformity

conformity CE
RoHS

dimension drawing

