Vision sensors

VS ID110M03W10EP

ID110

Article number: 11048484

overview

- User management
- Password protection
- Backup & Restore function
- Download *VeriSens*® Application Suite: www.baumer.com/vs-sw



technical data

general data	
resolution	752 × 480 px
sensor type	1/3″ CMOS, monochrome
illumination	integrated, LED white
LED class	risk group 1 (low risk, EN 62471:2008)
high-resolution mode	max. 50 inspections per second
object distance min.	50 mm
number of jobs (products)	≤ 255
features per job	32
signal processing	Baumer *FEX*® 3.5
defect image memory	32
lens	10 mm
electrical data	
voltage supply range +Vs	18 … 30 V DC
power consumption	typical 5 W (I_{max} = 1 A at 24 V)
digital inputs	5 inputs (8 … 30 V) trigger job selection external teach-in encoders (CH-A, CH-B) 500 kHz
digital outputs	5 outputs (PNP) Pass / Fail Flash Sync Alarm Camera Ready Output Enable
initial setup	Ethernet (10BASE-T / 100BASE-TX)
process interface	TCP/UDP (Ethernet)
visualization	web interface

mechanical data	
width	53 mm
height	99,5 mm
depth	38 mm
weight	≤ 250 g
material	housing: aluminum cover glass: PMMA
environmental conditions	
operating temperature	+5 … +50 °C
storage temperature	-20 … +70 °C
case temperature	max. +50 °C
humidity	0 … 90 % (non-condensing)
protection class	IP 67
vibration load	IEC 60068-2-6 IEC 60068-2-64
mechanical shock resistance	EN 60068-2-27
code types	
barcode	2/5 Industrial 2/5 Interleaved Codabar Code 39 Code 93 Code 128 PharmaCode EAN 8 EAN 13 UPC-A UPC-E GS1 DataBar GS1 128

2020-01-20 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.

Vision sensors

VS ID110M03W10EP

ID110

Article number: 11048484

technical data

code types

matrix code	DataMatrix (ECC 200) GS1-DataMatrix QR-Code PDF417
font	many font styles (recommended: sans serif, proportional) Dot Matrix characters: A-Z a-z 0-9 + - . : / ( )

feature checks

part location	part location on text line

feature checks

feature comparison	contour comparison
identification	barcode matrix code text

conformity

conformity	CE RoHS

non-volatile memory

flash memory size	256 Mbit Flash S29GL256P10FFI010

Electrical connection




1:	PWR (+18-30 V DC)	7:	OUT3
2:	Ground	8:	IN3
3:	IN1 (Trigger)	9:	OUT4
4:	OUT1	10:	IN4
5:	IN2	11:	IN5
6:	OUT2	12:	OUT5



1:	TD+	3:	TD-
2:	RD+	4:	RD-

dimension drawing



2020-01-20 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.