VLG-22M.I

Gigabit Ethernet, 2,0 Megapixel, Monochrome

Article number: 11104900

overview

- 2040 × 1084 pxams (CMOSIS) CMV20002/3" CMOS
- 55 fps
- Gigabit Ethernet
- available





technical data			
sensor information		camera features	
sensor	ams (CMOSIS) CMV2000	sequencer parameter	exposure time gain factor output ROI Offset x ROI Offset y
resolution	2040 × 1084 px		
exposure time	0,015 1000 ms		
pixel size	5.5 × 5.5 μm		
shutter type	Global shutter	digital inputs	1 input line
sensor type	2/3" CMOS	digital outputs	3 output lines
acquisition formats		internal image buffer	120 MB
image formats, interface	Full Frame, 2040 × 1084 px, max. 55 fps	interfaces and connectors	
frame rate max. pixel formats	Mono8 Mono12 Mono12 Packed	data interface	Gigabit Ethernet, Transfer rate 1000 Mbits/sec, Fast Ethernet, Transfer Rate 100 Mbits/sec, Connector: SACC-CI- M12FS-8CON-L180-10G
image preprocessing		process interface / power	SACC-CI-M12MS-8CON-SH TOR 32 / 8
analog controls	Gain (0 18 dB) Offset (0 255 LSB 12 Bit)	supply mechanical data	pins
color models	Mono	lens mount	C-mount
camera features		width	46 mm
synchronization	free running	height	46 mm
	trigger	depth	49.8 mm
trigger sources	Hardware software ActionCommand	weight	≤ 185 g ≤ 220 g (incl. tube)
trigger delay	0 2 sec, tracking and buffering of up to 512 trigger signals	material	aluminum, IP 65 / 67
		electrical data	
sequencer	Automated control for series of images using different sets of parameters	voltage supply range +Vs	12 24 V DC (external power supply) 36 57 V DC (Power over Ethernet)



VisiLine series

VLG-22M.I

Gigabit Ethernet, 2,0 Megapixel, Monochrome

Article number: 11104900

technical data		
electrical data		
power consumption	approx. 3,5 W @ 12 VDC and 55,0 fps approx. 3,8 W @ 48 VDC (PoE) and 55,0 fps	
non-volatile memory		
flash memory size	128 kB	
environmental conditions		
operating temperature	+5 +50 °C	
humidity	10 90 % (non-condensing)	
protection class	IP 40 IP 54 (with mounted tube and cable) IP 65 (with mounted tube and cable) IP 67 (with mounted tube and cable) IP 69K (with stainless steel housing ac-	

digital I/Os		
lines	1 input line	
	3 output lines	
conformity		
conformity	CE	
	RoHS	

dimension drawing



cessory)