

ZVI-RONDOLX_24VDC_IR850NM_120°

RONDO-LX IR 850nm 120° 24VDC with M8 connector

Article number: 11130150

overview

- flashable LED ring light
- infrared (850 nm)
- radiation angle 120°
- 24 V
- M8/4-pin connector (cable has to be ordered separately)
- diameter: 101 mm



technical data

general data

manufacturer BÜCHNER Lichtsysteme GmbH

illumination data

color infrared

electrical data

number of poles 4

illumination connector • M8 connector

current 0,35 A

current at flash mode ≤ 0,35 A

voltage at flash mode ≤ 48 V DC

duty cycle 0-10%

electrical data

maximum flash duration 1 ms

mechanical data

construction design ring light

dimensions Ø 101 mm

height 24 mm

dimensions luminous area Ø external 101 mm Ø internal 67 mm

material of cover glass acrylic

weight ≤ 160 g

material aluminum (anodized)

environmental conditions


operating temperature max. 50 °C

ZVI-RONDOLX_24VDC_IR850NM_120°


RONDO-LX IR 850nm 120° 24VDC with M8 connector

Article number: 11130150

dimension drawing



pin assignment



M8	signal
1:	LED +24V (pulsing 24-48 V)
2:	N.C.
3:	LED - (GND)
4:	N.C.