

overview

- User management
- Password protection
- Backup & Restore function
- Download VeriSens® Application Suite: www.baumer.com/vs-sw



technical data

general data

resolution	752 × 480 px
sensor type	1/3" CMOS, monochrome
illumination	integrated, LED white
LED class	risk group 1 (low risk, EN 62471:2008)
high-resolution mode	max. 50 inspections per second
object distance min.	70 mm
object distance max.	300 mm
number of jobs (products)	≤ 255
features per job	32
signal processing	Baumer FEX® 3.5
defect image memory	32
lens	16 mm

electrical data

voltage supply range +Vs	18 ... 30 V DC
power consumption	typical 5 W ($I_{max} = 1$ A at 24 V)
digital inputs	5 inputs (8 ... 30 V) trigger job selection external teach-in encoders (CH-A, CH-B) 500 kHz

electrical data

digital outputs	3 outputs (PNP) Pass / Fail Flash Sync Alarm Camera Ready Output Enable
initial setup	Ethernet (10BASE-T / 100BASE-TX)
process interface	TCP/UDP (Ethernet) RS485
visualization	web interface

mechanical data

width	53 mm
height	99,5 mm
depth	38 mm
weight	≤ 250 g
material	housing: aluminum cover glass: PMMA

environmental conditions

operating temperature	+5 ... +50 °C
storage temperature	-20 ... +70 °C
case temperature	max. +50 °C
humidity	0 ... 90 % (non-condensing)
protection class	IP 67
vibration load	IEC 60068-2-6 IEC 60068-2-64

VS ID100M03W16RP

ID100

Article number: 11076263

technical data

environmental conditions

mechanical shock resistance EN 60068-2-27

code types

barcode
2/5 Industrial
2/5 Interleaved
Codabar
Code 39
Code 93
Code 128
PharmaCode
EAN 8
EAN 13
UPC-A
UPC-E
GS1 DataBar
GS1 128

code types

matrix code
DataMatrix (ECC 200)
GS1-DataMatrix
QR-Code
PDF417

feature checks

identification
barcode
matrix code

conformity

conformity
CE
KC (R-REI-BkR-VeriSens-RP)
RoHS


non-volatile memory

flash memory size
256 Mbit Flash S29GL256P10FFI010

Electrical connection



1: PWR (+18-30 V DC)	7: OUT3
2: Ground	8: IN3
3: IN1 (Trigger)	9: RS485+
4: OUT1	10: IN4
5: IN2	11: IN5
6: OUT2	12: RS485-



1: TD+	3: TD-
2: RD+	4: RD-

dimension drawing

