

ZVI-TOPLINED1_24VDC_ROT617NM_30°

TOP-LINE-D1 red 617nm 30° 24VDC M8 1-canal

Article number: 11130187

overview

- flashable LED bar light
- red (617 nm)
- radiation angle 30°
- 24 V
- M8/4-pin connector (cable has to be ordered separately)
- dimensions: 78 mm × 25 mm × 23 mm housing



technical data

general data

manufacturer Büchner Lichtsysteme GmbH

illumination data

color red (617 nm)

electrical data

number of poles 4
illumination connector • M8 connector
current 0,2 A
current at flash mode ≤ 0,2 A
voltage at flash mode ≤ 48 V DC

electrical data

duty cycle 0-10%
maximum flash duration 1 ms


mechanical data

construction design bar light
dimensions 78 mm × 25 mm × 23 mm
material of cover glass acrylic
weight ≤ 80 g
material aluminum (anodized)

environmental conditions

operating temperature max. 50 °C

dimension drawing




ZVI-TOPLINED1_24VDC_ROT617NM_30°

TOP-LINE-D1 red 617nm 30° 24VDC M8 1-canal

Article number: 11130187

pin assignment



M8 signal

1: LED +24V (pulsing 24-48 V)

2: N.C.

3: LED - (GND)

4: N.C.