

GigE Power Switch Extended

Article number: 11008794

overview

- GigE switch
- PoE and Jumbo Frame support
- 5x 1000base-T
- 1x SFP module
- DIN rail mounting
- operating voltage: 24-48 V; PoE requires 48 V



technical data

electrical data

| | |
|----------------------|--|
| power supply | 48 VDC |
| power consumption | approx. 6 W |
| PoE class | <ul style="list-style-type: none"> • class 0 (at 48 V PoE) |
| supply | <ul style="list-style-type: none"> • up to 15,4 Watt |
| protective functions | <ul style="list-style-type: none"> • protection against polarity reversal disconnection on overload / overtemperature |

functionality

| | |
|------------------------|-----------------------------|
| auto crossover | yes |
| auto negotiation | yes |
| auto polarity | yes |
| supported packet size | Jumbo Frames up to 10 kByte |
| mechanical data | |
| mounting | DIN Rail |
| dimensions | 45 mm × 99 mm × 113,5 mm |
| material of housing | plastic |
| weight | ≤ 222 g |

interface

| | |
|-----------------------|---------------------------------------|
| data interface | GigE |
| Ethernet type | 1000base-T, 100base-TX, 10base-T |
| number of ports | 6 |
| ports | 5x RJ45, 1x SFP |
| standard | IEEE802.3 |
| transfer rate | 10 / 100 / 1000 MBit/sec |
| distance | max. 100 m |
| supported SFP modules | 1000base-LX, 1000base-SX, 1000base-TX |

environmental conditions

| | |
|-----------------------|------------------------------|
| operating temperature | +5 ... +40 °C |
| conformity | CE RoHS |
| storage temperature | -10 ... -70 °C |
| humidity | 10 ... 90 % (non-condensing) |
| protection class | IP 20 |