

overview

- 2592 × 1944 px
- ON Semiconductor MT9P031
- 1/2.5" CMOS
- 13 fps
- Gigabit Ethernet
- Phase-Out starting 09/19, alternative via sales



technical data

sensor information

sensor	ON Semiconductor MT9P031
resolution	2592 × 1944 px
exposure time	0,004 ... 1000 ms
pixel size	2.2 × 2.2 µm
shutter type	Rolling shutter
sensor type	1/2.5" CMOS

acquisition formats

image formats, interface frame rate max.	Full Frame, 2592 × 1944 px, max. 13 fps Binning 2×2, 1296 × 972 px, max. 33 fps Binning 4×4, 648 × 486 px, max. 52 fps
pixel formats	Mono8 Mono12 Mono12 Packed

image preprocessing

analog controls	Gain (0 ... 18 dB) Offset (0 ... 4095 LSB 12 Bit)
color models	Mono

camera features

synchronization	free running trigger
trigger sources	Hardware software ActionCommand
trigger delay	0 ... 2 sec, tracking and buffering of up to 512 trigger signals
digital inputs	1 input line (with Debouncer)
digital outputs	1 output line

camera features

internal image buffer	32 MB
-----------------------	-------

interfaces and connectors

data interface	Gigabit Ethernet, Transfer rate 1000 Mb/s/sec, Connector: 8P8C Modular Jack (RJ45), screwable type
process interface	M8 / 4 pins
power supply	M8 / 3 pins

mechanical data

lens mount	C-mount
width	36 mm
height	36 mm
depth	42 mm
weight	≤ 90 g
material	housing: aluminum

electrical data

voltage supply range +Vs	8 ... 30 V DC
power consumption	approx. 2,7 W

non-volatile memory

flash memory size	128 kB
-------------------	--------

environmental conditions

operating temperature	+5 ... +50 °C
humidity	10 ... 90 % (non-condensing)
protection class	IP 40

EXG50

Gigabit Ethernet, 5 Megapixel, Monochrome

Article number: 11012594

technical data

conformity

conformity	CE
	RoHS
	FCC
	KC (MSIP-REI-BkR-EXG50)
	EAC

dimension drawing

