

overview

- 1920 x 1200 px
- ON Semiconductor PYTHON2000
- 2/3" CMOS
- 167 fps
- USB 3.0
- available



technical data

sensor information

sensor	ON Semiconductor PYTHON2000
resolution	1920 × 1200 px
exposure time	0,02 ... 1000 ms
pixel size	4.8 × 4.8 µm
shutter type	Global shutter
sensor type	2/3" CMOS

acquisition formats

image formats, interface frame rate max.	Full Frame, 1920 × 1200 px, max. 167 fps Binning 2×2, 960 × 600 px, max. 167 fps Binning 2×1, 960 × 1200 px, max. 167 fps Binning 1×2, 1920 × 600 px, max. 167 fps
image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 1920 × 1200 px, max. 167 fps

pixel formats	BayerRG8 BayerRG10 BayerRG12 BayerRG12 Packed Mono8 Mono10 Mono12 Mono12 Packed RGB8 BGR8
---------------	--

image preprocessing

analog controls	Gain (0 ... 12 dB) Offset (0 ... 63 LSB 10 Bit)
-----------------	--

image preprocessing

color models	Mono Raw Bayer RGB
--------------	--------------------------

camera features

synchronization	free running trigger
trigger sources	Hardware software
trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals
internal image buffer	475 MB 72 images (Trigger Mode) 1 image (Free Running Mode)

interfaces and connectors

data interface	USB 3.0, Transfer Rate 5000 Mbits/sec, Connector: USB 3.0 Micro B
process interface	M8 / 8 pins (SACC-DSI-M8MS-8CON-M8-L180)
power supply	via USB 3.0 interface

mechanical data

lens mount	C-mount
width	29 mm
height	29 mm
depth	38 mm
weight	≤ 90 g
material	zinc die casting, baked varnish (until 02-2020 nickel-chrome-plated), IP 40

technical data

electrical data

power consumption	approx. 3,8 W @ 167 fps
operating voltage	5 VDC (via USB3.0 interface)

non-volatile memory

flash memory size	128 kB
-------------------	--------

environmental conditions

operating temperature	0 ... +65 ° @ T = measurement point
humidity	10 ... 90 % (non-condensing)
protection class	IP 40

digital I/Os

lines	1 input line
	1 output line
	2 general purpose lines

conformity

conformity	CE RoHS EAC
------------	-------------------

dimension drawing

