OR18.EL-PV1P.7BO

Through beam sensors - standard Article number: 11157817

Overview

- receiver
- through beam sensor
- 55 m
- PNP complementary
- potentiometer, 270°
- connector M12 4 pin
- -10 ... 55 °C
- IP 67



Picture similar






Technical data	
General data	
Туре	Through beam sensor
Emitter / receiver	Receiver
Actual range Sb	55 m
Nominal range Sn	60 m
Output indicator	LED yellow
Power on indication	LED green
Sensitivity adjustment	Potentiometer, 270°
Electrical data	
Response time / release time	< 0,34 ms
Voltage supply range +Vs	10 30 VDC
Current consumption max. (no load)	45 mA
Current consumption typ.	35 mA
Voltage drop Vd	< 2 VDC

Electrical data	
Output function	Light / dark operate
Output circuit	PNP complementary
Output current	< 100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes
Mechanical data	
Width / diameter	18 mm
Height / length	81,5 mm
Туре	Cylindrical threaded
Housing material	Brass nickel plated
Front (optics)	PMMA
Connection types	Connector M12 4 pin
Ambient conditions	
Operating temperature	-10 +55 °C
Protection class	IP 67

OR18.EL-PV1P.7BO

Through beam sensors - standard Article number: 11157817

Dimension drawing



Connection diagram



Laser warning

CLASS 1 LASER PRODUCT

IEC 60825-1/2014
Complies with 21 CFR 1040.10 and 1040.11 except for conformance with IEC 60825-1 Ed. 3., as described in Laser Notice No. 56, dated May 8, 2019

Pin assignment

