

Technical Data VCXU-50MP

Digital Monochrome polarized Matrix Camera, 5 Megapixel, **USB 3.0** Article No. 11206488 Firmware Revision 2.1














Model Name	Sony IMX250MZR
Туре	2/3" progressive scan CMOS
Shutter	Global Shutter
Resolution	2448 x 2048 pixels
Scan Area	8.44 mm x 7.06 mm
Pixel Size	3.45 µm x 3.45 µm




Data Quality	@ 20 °C, gain = 1, exposure time = 4 msec
Dark Noise (σ)	2 e- typical
Saturation	9500 e- typical
Dynamic Range	71 dB typical
SNR	40 dB typical
Quantum efficiency η	25% @ 536 nm typical

Acquisition

Resolution	2448 px x 2048 px		
Interface Frame Rate (depends on used interface	Format	Resolution	max. Frame Rate (@ Trigger Mode) 2)
performance)	Full Frame	2448 x 2048	73 fps
	Binning 2x2	1224 x 1024	77 fps
	Binning 2x1	1224 x 2048	77 fps
	Binning 1x2	2448 x 1024	77 fps
Acquisition Frame Rate 1)	77 fps $t_{readout} = 13 n$	NSEC (max. Res. Full Fra	ame) @ 10 bit
	68 fps t _{readout} = 14.6	msec (max. Res. Full	Frame) @ 12 bit
	77 fps t _{readout} = 13 n	nsec (max. Res. Binning	g 2x2) @ 10 bit
	68 fps t _{readout} = 14.6	msec (max. Res. Binn	ning 2x2) @ 12 bit
Pixel Formats	Mono8, Mono10, Mo		,
Partial Scan	True Partial Scan with increasing Frame Rate on Y		
	direction, Region of	Interest (ROI) arbit	rary
	Width: minimum 16,		
Adjustable Association	Heigth: minimum 2, Off or 0.01 4016		
Adjustable Acquisition Frame Rate	Off or 0.01 4016	ΠZ	
Acquisition Mode	Continuous, Single I	Frame and Multi Fr	ame
Acquisition Status	AcquisitionActive, A	cquisitionTrigger W	/ait
Exposure Mode	Timed		
Shutter Mode	-		
Readout Mode	Overlapped, Sequer	ntial	










Image Pre-Processing


minage i ie i ieeeeemig	
Analog Controls	Exposure Time (1 µsec 60 sec Step Size 1 µsec) Gain (048 dB), Offset (0 255 LSB 12 bit)
Gamma Correction	Gamma (0.1 2 available if LUT is enabled)
LUT	Luminance (12 bit)
Color Models	Mono
Color Processing	-
Color Adjustment	-
Color Enhancement	-
Color Tolerance	-
Binning Horizontal	1 or 2
Binning Vertical	1 or 2
Image Flipping	Horizontal, vertical
Defect Pixel Correction	via Defect Pixel List with up to 512 Pixel Coordinates
Fix Pattern Noise	-
Correction	


¹⁾ Sensor readout, different from pixel format

²⁾ depends on the used interface









Process Synchronization

· · · · · · · · · · · · · · · · · · ·		
Trigger Mode	Off (Free Running), On (Trigger)	
Trigger Overlap Type	Readout	
Trigger Sources	Hardware (Line0,1,2), Software, All or Off	
	fixed Trigger Delay out of treadout: 1)	
	51.8 µsec @ 10 bit	
	53.9 µsec @ 12 bit	
	max. Trigger Delay during treadout: 1)	
	52.8 µsec @ 10 bit	
	55.9 µsec @ 12 bit	
Trigger Delay	0 2 sec, Tracking and buffering of up to 256 triggers	
External Flash Sync	via Exposure Active	
	$t_{delay flash} \le 3 \mu sec, t_{duration} = t_{exposure}$	

Digital I/Os

Lines	Input: Line 0, Output: Line3, GPIO: Line 1, Line 2
Output Sources	Off, ExposureActive, Timer1, ReadoutActive,
	UserOutput 1-3 and TriggerReady
Line Debouncer	Low and high signal separately selectable
	Debouncing Time 0 5 msec, Step Size: 1 µsec

Memory

Image Buffer	445 MB
	31 Images (Trigger Mode) / 1 Image (Free Running Mode)
Non-volatile Memory	128 kb


Interface Data


Interface	USB3.0 (5000 Mbits/sec)
USB Vendor ID / Product ID	0x2825 / 0x12A


USB 3 Vision® Features


Events Transmission via Asynchronous Message Channel	DeviceTemperatureStatusChanged, EventLost, ExposureEnd, ExposureStart, FrameEnd, FrameStart, FrameTranferSkipped, Line03 FallingEdge, Line03 RisingEdge, TransferBufferFull, TransferBufferReady, TriggerOverlapped, TriggerReady, TriggerSkipped
Frame Counter	up to 2 ³²
Payload Size	0 10027208 Byte
Timestamp	64 bit
USB Vision	v1.0.1

¹⁾ Sensor readout, different from pixel format









Interfaces and Connectors

Data and Power Interface	USB 3.0 USB 2.0 Connector:	Transfer Rate 5000 Mbits/sec Transfer Rate 480 Mbits/sec USB 3.0 Micro B	
	Pin Assignment:	1 - VBUS 2 - D- 3 - D+ 4 - ID 5 - GND	6 - MicB_SSTX- 7 - MicB_SSTX+ 8 - GND_DRAIN MicB_SSRX- MicB_SSRX+
Process Interface	Connector: Assignment:	M8/8-pin (SACC-DSI-II 1 - GPIO (Line2) 2 - not connected 3 - IN1 (Line0) 4 - GND IN1	5 - Power VCC OUT1 6 - OUT1 (Line3) 7 - GND GPIO 8 - GPIO (Line1)

Caution



* Note GPIOs: Ground loops are to be avoided and can lead to destruction of the device.

Optical Data

Optioni Data	
Lens Mount	C-Mount
Optical Filter	-

Mechanical Data

Mechanical Data		
Housing	Zinc die casting, nickel-chrome-plated, IP40 (with mounted	
	lens and USB 3.0 cable)	
Protection Class	IP40 (with mounted lens and USB 3.0 cable)	
Weight	90 g	
Dimensions	2 x M3 x 4	
	temperature measurement point 6,15 8 29 18 2 x M2 x 4	
	3 8 8	

Environmental Data

Storage Temperature	-10 °C + 70 °C
Operating Temperature	+5 °C +65 °C @ T = Measurement Point or +5 °C +72 °C @ internal Temperature Sensor Ambient temperature above 30 °C requires heat dissipation measures.
Int. Temperature Sensor	yes, accuracy: ±1 °C (typ) 0 °C +85 °C
Humidity	10 % 90 % non-condensing

The maximum temperature for Sony sensor characteristics (sensor performance) are guaranteed up to 50°C @ Measurement Point or 56°C @ internal temperature sensor

LED Signalling

LED	Green flash	Power on, no link active
	Green	Link active USB 3.0
	Red	Error or Link active USB 2.0
	Yellow	Sensor Readout activity
	Red flash	Update

Electrical Data

Licotifical Data	
Power Supply	bus powered via USB3.0 interface
Power Consumption	approx. 3.3 W @ 73 fps
	(Factory Setting "Default")
Digital Input	Optocoupler
	U _{IN(low)} : 0.0 4.5 VDC
	U _{IN(high)} : 11.0 30.0 VDC
	I _{IN} : 3.0 10.0 mA
	min. Impulse Length: 2.0 µsec
Digital Output	Optocoupler
	U _{EXT} : 5 30 V DC
	I _{OUT} : max. 50 mA
	$t_{ON} = typ. 3 \mu sec$ $t_{OFF} = typ. 40 \mu sec$
GPIO	direct, without optocoupler
GPIO used as Input:	U _{IN(low)} : 0.0 0.8 VDC
	U _{IN(high)} : 2.0 30.0 VDC
	min. Impulse Length: 2.0 µsec
GPIO used as Output:	U _{Out(low)} : 0.0 0.4 VDC (I _{sink max} : 50 mA)
	U _{Out(high)} : 2.4 3.3VDC (I _{max} : 1 mA)
Caution	* The General Purpose I/Os (GPIOs) are not potential-free and do not
A	have an overrun cut-off. Incorrect wiring (overvoltage, undervoltage or
4	voltage reversal) can lead to defects in the electronic system. Ground loops are to be avoided and can lead to destruction of the device.
	Ground loops are to be avoided and can lead to destruction of the device.

Conformity

Conformity	CE, RoHS, REACH
KC Registration No. / Date	-/-
MTBF	56 years @ T = 45 °C / 36 years @ T = 60 °C
	T = Measurement Point

GenlCam[™] Features

Short Exposure Range	yes, ShortExposureTimeEnable	
Chert Exposure Hange	Short Exposure Range 1 µsec 60 sec	
	Default Exposure Range 15 µsec 60 sec	
Timer	Timer Selector: Timer Selector: Timer 1	
	TimerTriggerSource:	
	Line0, SoftwareTrigger, ExposureStart, ExposureEnd,	
	FrameTransferSkipped, TriggerSkipped, Off	
	TimerDelay: 0 µsec 2 sec, Step Size: 1 µsec	
	TimerDuration: 4 µsec 2 sec, Step Size: 1 µsec	
Counter	Counter Selector: Counter 1, Counter 2	
Counter.	CounterValue: 0 65535	
	Counter Event Source: Counter1End or Counter2End,	
	ExposureActive, FrameTransferSkipped, FrameTrigger,	
	TriggerSkipped and Off	
	Counter Reset Source: Counter1End, Counter2End, Line0	
	and Off	
Sequencer	Sequencer Characteristics:	
	up to 128 sets,	
	up to 4 possible pathes for triggered set transitions,	
	6 trigger sources: Counter1End, Counter2End,	
	ExposureActive, Line0, ReadoutActive, Timer1End	
	Sequencer Parameters for Exposure, Gain, Trigger, ROI	
	and Output:	
	ExposureTime, CounterDuration, CounterEventActivation,	
	CounterEventSource, CounterResetSource,	
	ExposureMode, ExposureTime, Gain, Height, OffsetX,	
	OffsetY, TriggerMode, UserOutputValue,	
	UserOutputValueAll, Width	

GenlCam[™] Features

User Sets	Factory Settings: UserSet0 (read only) Freely Programmable: UserSet1, UserSet2, UserSet3 Parameters: any user definable Parameter	
Acquisition Abort	Delay up to 14.6 msec	
Chunk Data	yes, Chunk Selector: Binning, Black Level, DeviceTemperature, ExposureTime, FrameID, Gain, Height, Image, ImageControl, LineStatusAll	
Device Temperature	InHouse Event generation for Normal to High, High to Exceeded and Exceeded to Normal Exceeded (no image transfer) = max. internal temperature sensor + 1 °C	
Device Link Throughput Limit	yes, up to max. Device Link Speed	
SFNC Version	v2.3	

Factory Settings after Start-Up

i actory bettings after	i Start-Op
Trigger Mode	Off (Free Running)
Analog Controls	Exposure Time: 4 msec, Gain: 0 dB, Offset: 0
Pixel Format	Mono8
Partial Scan	Off
Acquisition Frame Rate	Off
Timer/Counter/Sequencer	Off
Defect Pixel Correction	ON
Fixed Pattern Noise	-
Correction	
Digital Input	Line0, invert = false
Digital Output	Line3, invert = false, line source = Off
GPIO 1/2	Line1, Line2, invert = false, LineMode = Input
TriggerSource	All

Partial Scan @ FullFrame, min Exposure, Mono8 or BayerRG8

F	Resolution	max. fps acquisition	max. fps interface 2)
Full HD	1920 x 1080	143	143
SXGA	1280 x 1024	150	150
XGA	1024 x 768	198	198
SVGA	800 x 600	250	250
VGA	640 x 480	307	307
CIF	352 x 288	486	486
QCIF	176 x 144	860	859
LineScan	2448 x 2048	76	73
	2448 x 1024	150	146
	2448 x 512	290	290
	2448 x 256	538	538
	2448 x 128	940	940
	2448 x 64	1502	1490
	2448 x 32	2143	2058
	2448 x 16	2719	2638
	2448 x 8	3147	3030
	2448 x 4	3417	3389
	2448 x 2	3562	3405
	2448 x 1	-	-

²⁾ depends on the used interface