

# OBDM 12N6950/S35A

Difference sensors Article number: 10158757

#### Overview

- 2-point comparison
- 16 ... 120 mm
- pulsed red laser diode
- NPN
- Teach-in
- connector M8 4 pin
- 50 °C
- IP 67



Picture similar







Technical data	
General data	
Туре	2-point comparison
Sensing distance Tw	16 120 mm
Teach-in range min.	> 0,3 mm
Adjustment	Teach-in
Power on indication	LED green
Output indicator	LED red
Light source	Pulsed red laser diode
Laser class	2
Wave length	650 nm
Beam diameter	0,5 0,2 mm
Electrical data	
Response time	< 1 ms
Voltage supply range +Vs	12 28 VDC
Current consumption max. (no load)	80 mA
Current consumption typ.	40 mA


Electrical data	
Output circuit	NPN
Output current	< 100 mA
Voltage drop Vd	< 2,8 VDC
Reverse polarity protection	Yes, Vs to GND
Short circuit protection	Yes
Mechanical data	
Width / diameter	12,4 mm
Height / length	37 mm
Depth	34,5 mm
Туре	Rectangular
Front (optics)	Glass
Housing material	Die-cast zinc
Connection types	Connector M8 4 pin
Ambient conditions	
Operating temperature	0 +50 °C
Protection class	IP 67

# OBDM 12N6950/S35A


Difference sensors

Article number: 10158757

### **Dimension drawing**



### **Connection diagram**



### Laser warning



LASER RADIATION
DO NOT STARE INTO BEAM
Wavelength: 640...670nm

IEC 60825-1, Ed. 3, 2014
CLASS 2 LASER PRODUCT

IEC 60825-1/2014 Complies with 21 CFR 1040.10 and 1040.11 except for conformance with IEC 60825-1 Ed. 3., as described in Laser Notice No. 56, dated May 8, 2019