# **OZDK 10P5101**

Diffuse sensors with intensity difference - miniature

Article number: 10136501

### Overview

- intensity difference
- 3 ... 150 mm
- pulsed red laser diode
- PNP
- potentiometer, 5 turn
- cable 4 pin, 2 m
- -10 ... 50 °C
- IP 65



Picture similar







Technical data	
General data	
Туре	Intensity difference
Light source	Pulsed red laser diode
Sensing distance Tw	3 150 mm
Optimum operating distance	20 40 mm
Detectable remission difference (on grey)	> 8 %
Repeat accuracy	< 0,2 mm at laser focus
Power on indication	LED green
Light indicator	LED yellow
Sensitivity adjustment	Potentiometer, 5 turn
Laser class	2
Distance to focus	40 mm
Wave length	650 nm
Electrical data	
Response time / release time	< 0,05 ms
Voltage supply range +Vs	10 30 VDC
Current consumption max. (no load)	50 mA


Electrical data	
Current consumption typ.	40 mA
Voltage drop Vd	< 1,8 VDC
Output function	Light / dark operate
Output circuit	PNP
Output current	< 100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes
Mechanical data	
Width / diameter	10,4 mm
Height / length	27 mm
Depth	16,3 mm
Туре	Rectangular
Housing material	Plastic (ASA)
Front (optics)	PMMA
Connection types	Cable 4 pin, 2 m
Ambient conditions	
Operating temperature	-10 +50 °C
Protection class	IP 65

## **OZDK 10P5101**


Diffuse sensors with intensity difference - miniature

Article number: 10136501


#### **Dimension drawing**




### **Connection diagram**



### Laser warning



### Beam characteristic (typically)



### Relative receiving signal

