

LXG-20C

Dual GigE, 2 Megapixel, Color

Article number: 11137904

Overview

- 2048 × 1088 px
- ams (CMOSIS) CMV2000 V3
- 2/3" CMOS
- 111 fps
- Dual Gigabit Ethernet
- available



GEN*i*CAM



Technical data

Sensor information

Sensor	ams (CMOSIS) CMV2000 V3
Resolution	2048 × 1088 px
Exposure time	0,03 ... 1000 ms
Pixel size	5.5 × 5.5 µm
Shutter type	Global shutter
Sensor type	2/3" CMOS

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 2048 × 1088 px, max. 111 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 2048 × 1088 px, max. 337 fps
Pixel formats	BayerGB8 BayerGB10 BayerGB10 Packed

Image preprocessing

Analog controls	Gain (0 ... 12 dB) Offset (0 ... 63 LSB 10 Bit)
Color models	Raw Bayer
Color processing	NA

Camera features

Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals

Camera features

Sequencer	Automated control for series of images using different sets of parameters
Sequencer parameter	Exposure time gain factor Output ROI Offset x ROI Offset y
Digital inputs	1 input line
Digital outputs	3 output lines
Internal image buffer	512 MB

Interfaces and connectors

Data interface	Dual Gigabit Ethernet, Transfer rate 2000 Mbits/sec, Connector: 2 x 8P8C Modular Jack (RJ45), screwable type
Process interface	M8 / 8 pins
Power supply	via M8 / 8 pins

Mechanical data

Lens mount	C-mount
Width	60 mm
Height	60 mm
Depth	52,4 mm
Weight	≤ 340 g
Material	housing: aluminum

Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
--------------------------	--

LXG-20C

Dual GigE, 2 Megapixel, Color

Article number: 11137904

Technical data

Electrical data

Power consumption	approx. 6,2 W @ 24 VDC
	approx. 5,2 W @ 48 VDC (PoE)

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	+5 ... +64 °C @ T = measurement point
-----------------------	---------------------------------------

Environmental conditions

Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

Conformity

Conformity	CE
	RoHS
	EAC

Dimension drawing

