

LXG-20NIR

Dual GigE, 2 Megapixel, Monochrome/Enhanced NIR

Article number: 11137906

Overview

- 2048 × 1088 px
- ams (CMOSIS) CMV2000 V3
- 2/3" CMOS
- 111 fps
- Dual Gigabit Ethernet
- available



GEN<i>i>CAM



Technical data

Sensor information

Sensor	ams (CMOSIS) CMV2000 V3
Resolution	2048 × 1088 px
Exposure time	0,03 ... 1000 ms
Pixel size	5.5 × 5.5 µm
Shutter type	Global shutter
Sensor type	2/3" CMOS

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 2048 × 1088 px, max. 111 fps Binning 2×2, 1024 × 544 px, max. 336 fps Binning 1×2, 2048 × 544 px, max. 222 fps Binning 2×1, 1024 × 1088 px, max. 153 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 2048 × 1088 px, max. 337 fps
Pixel formats	Mono8 Mono10 Mono10 Packed

Image preprocessing

Analog controls	Gain (0 ... 12 dB) Offset (0 ... 63 LSB 10 Bit)
Color models	Mono NIR

Camera features

Synchronization	free running trigger
-----------------	-------------------------

Camera features

Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals
Sequencer	Automated control for series of images using different sets of parameters
Sequencer parameter	Exposure time gain factor Output ROI Offset x ROI Offset y
Digital inputs	1 input line
Digital outputs	3 output lines
Internal image buffer	512 MB

Interfaces and connectors

Data interface	Dual Gigabit Ethernet, Transfer rate 2000 Mbits/sec, Connector: 2 x 8P8C Modular Jack (RJ45), screwable type
Process interface	M8 / 8 pins
Power supply	via M8 / 8 pins

Mechanical data

Lens mount	C-mount
Width	60 mm
Height	60 mm
Depth	52,4 mm
Weight	≤ 340 g

LXG-20NIR

Dual GigE, 2 Megapixel, Monochrome/Enhanced NIR

Article number: 11137906

Technical data

Mechanical data

Material housing: aluminum

Electrical data

Voltage supply range +Vs 12 ... 24 V DC (external power supply)
36 ... 57 V DC (Power over Ethernet)

Power consumption approx. 6,2 W @ 24 VDC
approx. 5,2 W @ 48 VDC (PoE)

Non-volatile memory

Flash memory size 128 kB

Environmental conditions

Operating temperature +5 ... +64 °C @ T = measurement point

Humidity 10 ... 90 % (non-condensing)

Protection class IP 40

Conformity

Conformity CE
RoHS
EAC

Dimension drawing

