

VCXU-02M

USB 3.0, 0,3 Megapixel, Monochrome

Article number: 11165914

Overview

- 640 x 480 px
- ON Semiconductor PYTHON300
- 1/4" CMOS
- 891 fps
- USB 3.0
- available



Technical data

Sensor information

Sensor	ON Semiconductor PYTHON300
Mono/Color	Mono
Resolution	640 × 480 px
Exposure time	0,02 ... 1000 ms
Pixel size	4.8 × 4.8 µm
Shutter type	Global shutter
Sensor type	1/4" CMOS

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 640 × 480 px, max. 891 fps Binning 2×2, 320 × 240 px, max. 891 fps Binning 2×1, 320 × 480 px, max. 891 fps Binning 1×2, 640 × 240 px, max. 891 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 640 × 480 px, max. 892 fps
Pixel formats	Mono8 Mono10

Image preprocessing

Analog controls	Gain (0 ... 12 dB) Offset (0 ... 63 LSB 10 Bit)
Color models	Mono

Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	Exposure Auto Gain Auto White Balance Auto Color Transformation Auto
Image Pre-processing	Image Flipping (X/Y) Color Processing (RGB, BGR, Mono) Color Enhancement (with optimized ColorTransformationMatrix) LUT / Gamma
Acquisition / Interface	Burst Mode Adjustable Framerate Device Link Throughput Limit Internal Image Buffer
Synchronization	free running trigger
Trigger sources	Hardware Software
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals

VCXU-02M

USB 3.0, 0,3 Megapixel, Monochrome

Article number: 11165914

Technical data

Camera features

Process Synchronization	Events Timer Triggerdelay Debouncer Counter Sequencer Trigger via Action CMD (GigE) Additional Output Modes (e.g. Trigger Ready) Chunkdata inside transferred image Encoder support via Counter End trigger source
Additional Functions	User Set Integrated temperature sensor Readable additional information (e.g. sensor information) Save Custom Data
Internal image buffer	436 MB 496 images (Trigger Mode) 1 image (Free Running Mode)

Interfaces and connectors

Data interface	USB 3.0, Transfer Rate 5000 Mbits/sec, Connector: USB 3.0 Micro B
Process interface	M8 / 8 pins (SACC-DSI-M8MS-8CON-M8-L180)
Power supply	via USB 3.0 interface

Mechanical data

Lens mount	C-mount
------------	---------

Mechanical data

Width	29 mm
Height	29 mm
Depth	38 mm
Weight	≤ 90 g
Material	zinc die casting, baked varnish (until 02-2020 nickel-chrome-plated), IP 40

Electrical data

Power consumption	approx. 2,5 W @ 891 fps
Operating voltage	5 VDC (via USB3.0 interface)

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	0 ... +65 ° @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

Digital I/Os

Lines	1 input line 1 output line 2 general purpose lines
-------	--

Conformity

Conformity	CE RoHS KC (MSIP-REI-BkR-VCXU13M) EAC
------------	--

Dimension drawing

