

VCXG-02M

Gigabit Ethernet, 0,3 Megapixel, Monochrome

Article number: 11165842

Overview

- 640 x 480 px
- ON Semiconductor PYTHON300
- 1/4" CMOS
- 403 fps
- Gigabit Ethernet
- available



GEN<i>i>CAM



Technical data

Sensor information

Sensor	ON Semiconductor PYTHON300
Mono/Color	Mono
Resolution	640 × 480 px
Exposure time	0,02 ... 1000 ms
Pixel size	4.8 × 4.8 µm
Shutter type	Global shutter
Sensor type	1/4" CMOS

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 640 × 480 px, max. 403 fps Binning 2×2, 320 × 240 px, max. 595 fps Binning 2×1, 320 × 480 px, max. 595 fps Binning 1×2, 640 × 240 px, max. 595 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 640 × 480 px, max. 573 fps
Pixel formats	Mono8 Mono10

Image preprocessing

Analog controls	Gain (0 ... 12 dB) Offset (0 ... 63 LSB 10 Bit)
Color models	Mono

Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	Exposure Auto Gain Auto White Balance Auto Color Transformation Auto
Image Pre-processing	Image Flipping (X/Y) Color Processing (RGB, BGR, Mono) Color Enhancement (with optimized ColorTransformationMatrix) LUT / Gamma
Acquisition / Interface	Burst Mode Adjustable Framerate Device Link Throughput Limit Internal Image Buffer
Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals

VCXG-02M

Gigabit Ethernet, 0,3 Megapixel, Monochrome

Article number: 11165842

Technical data

Camera features

Process Synchronization	Events Timer Triggerdelay Debouncer Counter Sequencer Trigger via Action CMD (GigE) Additional Output Modes (e.g. Trigger Ready) Chunkdata inside transferred image Encoder support via Counter End trigger source
Additional Functions	User Set Integrated temperature sensor Readable additional information (e.g. sensor information) Save Custom Data
Internal image buffer	15 MB 16 images (Trigger Mode) 1 image (Free Running Mode)

Interfaces and connectors

Data interface	Gigabit Ethernet, Transfer rate 1000 Mbits/sec, Fast Ethernet, Transfer Rate 100 Mbits/sec, Connector: 8P8C Modular Jack (RJ45), screwable type
Process interface	M8 / 8 pins (SACC-DSI-M8MS-8CON-M8-L180)
Power supply	via M8 / 8 pins or Power over Ethernet (PoE)

Mechanical data

Lens mount	C-mount
------------	---------

Mechanical data

Width	29 mm
Height	29 mm
Depth	49 mm
Weight	≤ 120 g
Material	zinc die casting, baked varnish (until 02-2020 nickel-chrome-plated), IP 40

Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
Power consumption	approx. 2,4 W @ 12 VDC and 403 fps approx. 2,9 W @ 48 VDC (PoE) and 403 fps

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	0 ... +65 ° @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

Digital I/Os

Lines	1 input line 1 output line 2 general purpose lines
-------	--

Conformity

Conformity	CE RoHS KC (MISP-REI-BKR-VCXG-13M) EAC
------------	---

Dimension drawing

