Baumer
Passion for Sensors

Inductive proximity switch

IFBR 11N37T1/L-9

Inductive proximity switch - hygiene

Article number: 11014611

Overview

- 4 mm
- NPN break function (NC)
- cable PVC, 2 m
- -40 … 80 °C
- IP 68/69K & proTect+



Picture similar

Technical data

General data	
Mounting type	Flush
Special type	Hygienic design
Nominal sensing distance Sn	4 mm
Hysteresis	2 … 15 % of Sr
Output indicator	LED red
Approvals/certificates	Ecolab EHEDG REGULATION (EC) 1935/2004 REGULATION (EC) 2023/2006 REGULATION (EU) 1282/2011 FDA 21 CFR § 175.300 FDA 21 CFR § 177.2600 FCN 742
Electrical data	
Switching frequency	< 1 kHz
Voltage supply range +Vs	6 … 30 VDC
Current consumption max. (no load)	10 mA

Electrical data	
Output circuit	NPN break function (NC)
Voltage drop Vd	< 2 VDC
Output current	< 200 mA
Output current (at cleaning temperature)	< 100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes
Mechanical data	
Type	Cylindrical smooth
Material (sensing face)	LCP
Housing material	Stainless steel 1.4404 (V4A); LSR
Dimension	11 mm
Housing length	54 mm
Connection types	Cable PVC, 2 m
Ambient conditions	
Operating temperature	-40 … +80 °C
Cleaning temperature	80 … +100 °C (30 min/day)
Protection class	IP 68/69K & proTect+

Remarks

- Sensor compliant with various food regulations (see approvals)
- LSR = Liquid Silicon Rubber

The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.
2021-04-28


Inductive proximity switch

IFBR 11N37T1/L-9


Inductive proximity switch - hygiene

Article number: 11014611

Dimension drawing



Connection diagram



2021-04-28 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.