

V CXU-31M

USB 3.0, 3,1 Megapixel, Monochrome

Article number: 11165812

Overview

- 2048 x 1536 px
- Sony IMX252
- 1/1.8" CMOS
- 117 fps
- USB 3.0
- available



GEN*i*CAM



Technical data

Sensor information

Sensor	Sony IMX252 Gen2
Mono/Color	Mono
Resolution	2048 × 1536 px
Exposure time	0,001 ... 60000 ms
Pixel size	3.45 × 3.45 µm
Shutter type	Global shutter
Sensor type	1/1.8" CMOS

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 2048 × 1536 px, max. 117 fps Binning 2×2, 1024 × 768 px, max. 120 fps Binning 2×1, 1024 × 1536 px, max. 120 fps Binning 1×2, 2048 × 768 px, max. 120 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 2048 × 1536 px, max. 120 fps
Pixel formats	Mono8 Mono10 Mono12 Mono12 Packed

Image preprocessing

Analog controls	Gain (0 ... 48 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	Mono

Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	Exposure Auto Gain Auto White Balance Auto Color Transformation Auto
Image Pre-processing	Image Flipping (X/Y) Color Processing (RGB, BGR, Mono) Color Enhancement (with optimized ColorTransformationMatrix) LUT / Gamma
Acquisition / Interface	Burst Mode Adjustable Framerate Short Exposure Time Enable Device Link Throughput Limit Internal Image Buffer
Synchronization	free running trigger
Trigger sources	Hardware Software
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals

VCXU-31M

USB 3.0, 3,1 Megapixel, Monochrome

Article number: 11165812

Technical data

Camera features

Process Synchronization	Events Timer Triggerdelay Debouncer Counter Sequencer Trigger via Action CMD (GigE) Additional Output Modes (e.g. Trigger Ready) Chunkdata inside transferred image Encoder support via Counter End trigger source
Additional Functions	User Set Integrated temperature sensor Readable additional information (e.g. sensor information) Save Custom Data
Internal image buffer	432 MB 48 images (Trigger Mode) 1 image (Free Running Mode)

Interfaces and connectors

Data interface	USB 3.0, Transfer Rate 5000 Mbits/sec, Connector: USB 3.0 Micro B
Process interface	M8 / 8 pins (SACC-DSI-M8MS-8CON-M8-L180)
Power supply	via USB 3.0 interface

Mechanical data

Lens mount	C-mount
------------	---------

Mechanical data

Width	29 mm
Height	29 mm
Depth	38 mm
Weight	≤ 90 g
Material	zinc die casting, baked varnish (until 02-2020 nickel-chrome-plated), IP 40

Electrical data

Power consumption	approx. 3,4 W @ 117 fps
Operating voltage	5 VDC (via USB3.0 interface)

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	0 ... +65 ° @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

Digital I/Os

Lines	1 input line 1 output line 2 general purpose lines
-------	--

Conformity

Conformity	CE RoHS KC (MISP-REI-BkR-VCXU-50M) EAC
------------	---

Dimension drawing

