Baumer
Passion for Sensors

Inductive proximity switch

IFFM 06N15A3/O1S05L

Inductive proximity switch - subminiature

Article number: 10146216

Overview

- 1 mm
- NPN make function (NO)
- connector M5
- -25 … 75 °C
- IP 67



Picture similar

Technical data

General data	
Mounting type	Flush
Nominal sensing distance Sn	1 mm
Hysteresis	2 … 20 % of Sr
Output indicator	2 port LED red
Electrical data	
Switching frequency	< 5 kHz
Voltage supply range +Vs	6 … 30 VDC
Current consumption max. (no load)	12 mA
Output circuit	NPN make function (NO)
Voltage drop Vd	< 2 VDC
Output current	< 200 mA

Electrical data	
Short circuit protection	Yes
Reverse polarity protection	Yes
Mechanical data	
Type	Rectangular
Material (sensing face)	LCP
Housing material	Brass nickel plated
Dimension	6 mm
Housing length	24 mm
Connection types	Connector M5
Ambient conditions	
Operating temperature	-25 … +75 °C
Protection class	IP 67

Remarks

- Short compact housing
- Miniature connector M5 x 5

2021-04-28 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.


Inductive proximity switch

IFFM 06N15A3/O1S05L


Inductive proximity switch - subminiature

Article number: 10146216

Dimension drawing



Connection diagram



2021-04-28 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.