

IFBR 17N33T1/S14L-9

Inductive proximity switch - hygiene

Article number: 11014607

Overview

- 12 mm
- NPN break function (NC)
- connector M12
- 40 ... 80 °C
- IP 68/69K & proTect+



Picture similar



Technical data

General data

Mounting type	Non-flush
Special type	Hygienic design
Nominal sensing distance S _n	12 mm
Hysteresis	2 ... 15 % of S _r
Output indicator	LED red
Approvals/certificates	Ecolab EHEDG

REGULATION (EC) 1935/2004
REGULATION (EC) 2023/2006
REGULATION (EU) 1282/2011
FDA 21 CFR § 175.300
FDA 21 CFR § 177.2600
FCN 742

Electrical data

Switching frequency	< 500 Hz
Voltage supply range +V _s	6 ... 30 VDC
Current consumption max. (no load)	10 mA

Electrical data

Output circuit	NPN break function (NC)
Voltage drop V _d	< 2 VDC
Output current	< 200 mA
Output current (at cleaning temperature)	< 100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes

Mechanical data

Type	Cylindrical smooth
Material (sensing face)	LCP
Housing material	Stainless steel 1.4404 (V4A); LSR
Dimension	17 mm
Housing length	60 mm
Connection types	Connector M12

Ambient conditions

Operating temperature	-40 ... +80 °C
Cleaning temperature	80 ... +100 °C (30 min/day)
Protection class	IP 68/69K & proTect+

Remarks


- Sensor compliant with various food regulations (see approvals)
- LSR = Liquid Silicon Rubber

IFBR 17N33T1/S14L-9

Inductive proximity switch - hygiene

Article number: 11014607

Dimension drawing



Connection diagram

