

## IFBR 17P17T1/L-9

Inductive proximity switch - hygiene

Article number: 11014616

### Overview

- 8 mm
- PNP make function (NO)
- cable PVC, 2 m
- 40 ... 80 °C
- IP 68/69K & proTect+



Picture similar



### Technical data

#### General data

|                                            |                                                                                                                                                                    |
|--------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Mounting type                              | Quasi-flush                                                                                                                                                        |
| Special type                               | Hygienic design                                                                                                                                                    |
| Nominal sensing distance<br>S <sub>n</sub> | 8 mm                                                                                                                                                               |
| Hysteresis                                 | 2 ... 15 % of S <sub>r</sub>                                                                                                                                       |
| Output indicator                           | LED red                                                                                                                                                            |
| Approvals/certificates                     | Ecolab<br>EHEDG<br>REGULATION (EC) 1935/2004<br>REGULATION (EC) 2023/2006<br>REGULATION (EU) 1282/2011<br>FDA 21 CFR § 175.300<br>FDA 21 CFR § 177.2600<br>FCN 742 |

#### Electrical data

|                                       |              |
|---------------------------------------|--------------|
| Switching frequency                   | < 500 Hz     |
| Voltage supply range +V <sub>s</sub>  | 6 ... 30 VDC |
| Current consumption max.<br>(no load) | 10 mA        |

#### Electrical data

|                                             |                        |
|---------------------------------------------|------------------------|
| Output circuit                              | PNP make function (NO) |
| Voltage drop V <sub>d</sub>                 | < 2 VDC                |
| Output current                              | < 200 mA               |
| Output current (at cleaning<br>temperature) | < 100 mA               |
| Short circuit protection                    | Yes                    |
| Reverse polarity protection                 | Yes                    |

#### Mechanical data

|                         |                                   |
|-------------------------|-----------------------------------|
| Type                    | Cylindrical smooth                |
| Material (sensing face) | LCP                               |
| Housing material        | Stainless steel 1.4404 (V4A); LSR |
| Dimension               | 17 mm                             |
| Housing length          | 55 mm                             |
| Connection types        | Cable PVC, 2 m                    |

#### Ambient conditions

|                       |                             |
|-----------------------|-----------------------------|
| Operating temperature | -40 ... +80 °C              |
| Cleaning temperature  | 80 ... +100 °C (30 min/day) |
| Protection class      | IP 68/69K & proTect+        |

### Remarks


- Sensor compliant with various food regulations (see approvals)
- LSR = Liquid Silicon Rubber

## IFBR 17P17T1/L-9

Inductive proximity switch - hygiene

Article number: 11014616

### Dimension drawing



### Connection diagram

