Baumer
Passion for Sensors

Inductive proximity switch

IFFM 08N17A5/O1S35L

Inductive proximity switch - subminiature

Article number: 10160245

Overview

- 2 mm
- NPN make function (NO)
- connector M8
- -25 … 75 °C
- IP 67



Picture similar

Technical data

General data	
Mounting type	Flush
Nominal sensing distance Sn	2 mm
Hysteresis	3 … 20 % of Sr
Output indicator	LED red
Electrical data	
Switching frequency	< 5 kHz
Voltage supply range +Vs	6 … 36 VDC
Current consumption max. (no load)	12 mA
Output circuit	NPN make function (NO)
Voltage drop Vd	< 2 VDC
Output current	< 200 mA

Electrical data	
Short circuit protection	Yes
Reverse polarity protection	Yes
Mechanical data	
Type	Rectangular
Material (sensing face)	PBT
Housing material	Die-cast zinc nickel plated
Dimension	8 mm
Housing length	27,4 mm
Connection types	Connector M8
Ambient conditions	
Operating temperature	-25 … +75 °C
Protection class	IP 67

The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.
2021-04-28


Inductive proximity switch

IFFM 08N17A5/O1S35L


Inductive proximity switch - subminiature

Article number: 10160245

Dimension drawing



Connection diagram



2021-04-28 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.