Baumer
Passion for Sensors

Inductive proximity switch

IFRM 04P35A1/L

Inductive proximity switch - subminiature

Article number: 10144584

Overview

- 1 mm
- PNP break function (NC)
- cable, 2 m
- -25 … 75 °C
- IP 67



Picture similar

Technical data

General data	
Mounting type	Flush
Nominal sensing distance Sn	1 mm
Hysteresis	2 … 20 % of Sr
Output indicator	LED red
Electrical data	
Switching frequency	< 5 kHz
Voltage supply range +Vs	6 … 30 VDC
Current consumption max. (no load)	12 mA
Output circuit	PNP break function (NC)
Voltage drop Vd	< 2 VDC
Output current	< 200 mA

Electrical data	
Short circuit protection	Yes
Reverse polarity protection	Yes
Mechanical data	
Type	Cylindrical smooth
Material (sensing face)	LCP
Housing material	Stainless steel
Dimension	4 mm
Housing length	25 mm
Connection types	Cable, 2 m
Ambient conditions	
Operating temperature	-25 … +75 °C
Protection class	IP 67

Remarks

- Standard execution with PUR cable
- 25 mm housing length

2021-04-28 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.


Inductive proximity switch

IFRM 04P35A1/L


Inductive proximity switch - subminiature

Article number: 10144584

Dimension drawing



Connection diagram



2021-04-28 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.