## IFRR 18P17T1/L-9

Inductive proximity switch - washdown

Article number: 11013639

### Overview

- 8 mm
- PNP make function (NO)
- cable PVC, 2 m
- -40 ... 80 °C
- IP 68/69K & proTect+



Picture similar







Technical data	
General data	
Mounting type	Quasi-flush
Special type	Washdown design
Nominal sensing distance Sn	8 mm
Hysteresis	2 15 % of Sr
Output indicator	LED red
Approvals/certificates	Ecolab
Electrical data	
Switching frequency	< 500 Hz
Voltage supply range +Vs	6 30 VDC
Current consumption max. (no load)	10 mA
Output circuit	PNP make function (NO)
Voltage drop Vd	< 2 VDC
Output current	< 200 mA
Output current (at cleaning temperature)	< 100 mA
Short circuit protection	Yes

Electrical data	
Reverse polarity protection	Yes
Mechanical data	
Туре	Cylindrical threaded
Material (sensing face)	LCP
Housing material	Stainless steel 1.4404 (V4A); LSR
Dimension	18 mm
Housing length	55 mm
Connection types	Cable PVC, 2 m
Tightening torque max.	55 Nm (Front: 38 Nm)
Ambient conditions	
Operating temperature	-40 +80 °C
Cleaning temperature	80 +100 °C (30 min/day)
Protection class	IP 68/69K & proTect+
Vibration resistance	EN 61373: 2010 (category 3), 5h per axis (14.4 gRMS, 10-500 Hz, EN 60068-2-64)
Shock resistance	EN 61373: 2010 (category 3), 10 bumps per axis (100 q, 6 ms, EN 60068-2-27)


- Sensor FDA compliant and Ecolab approved
- LSR = Liquid Silicon Rubber



# IFRR 18P17T1/L-9

Inductive proximity switch - washdown Article number: 11013639

## **Dimension drawing**



## Connection diagram

