

IFRP 12P1504/S14

Inductive sensors special versions - pressure resistant

Article number: 10143254

Overview

- 2 mm
- PNP make function (NO)
- connector M12
- -25 ... 80 °C
- IP 68/67 (sensing face/sensor)



Picture similar







| Technical data | |
|------------------------------------|------------------------|
| General data | |
| Mounting type | Flush |
| Special type | High pressure |
| Nominal sensing distance Sn | 2 mm |
| Hysteresis | 2 20 % of Sr |
| Electrical data | |
| Switching frequency | < 5 kHz |
| Voltage supply range +Vs | 6 30 VDC |
| Current consumption max. (no load) | 12 mA |
| Output circuit | PNP make function (NO) |
| Voltage drop Vd | < 2 VDC |
| Output current | < 200 mA |
| Short circuit protection | Yes |
| Reverse polarity protection | Yes |


| Mechanical data | |
|---------------------------------|--------------------------------|
| Туре | Cylindrical threaded |
| Material (sensing face) | Ceramic |
| Housing material | Stainless steel |
| Peak pressure | 1000 bar |
| Operating pressure static | < 500 bar |
| Operating pressure dy- namic | < 350 bar |
| Dimension | 12 mm |
| Housing length | 70 mm |
| Connection types | Connector M12 |
| Ambient conditions | |
| Operating temperature | -25 +80 °C |
| Protection class | IP 68/67 (sensing face/sensor) |

IFRP 12P1504/S14


Inductive sensors special versions - pressure resistant

Article number: 10143254

Dimension drawing



Installation drawing



Connection diagram

