Baumer
Passion for Sensors

Inductive proximity switch

IFRM 12P3703/S14L

Inductive proximity switch - standard

Article number: 10229703

Overview

- 4 mm
- PNP break function (NC)
- connector M12
- -25 … 75 °C
- IP 67



Picture similar

Technical data

General data	
Mounting type	Flush
Nominal sensing distance Sn	4 mm
Hysteresis	3 … 20 % of Sr
Output indicator	3 port LED red
Electrical data	
Switching frequency	< 2 kHz
Voltage supply range +Vs	6 … 36 VDC
Current consumption max. (no load)	10 mA
Output circuit	PNP break function (NC)
Voltage drop Vd	< 2 VDC
Output current	< 200 mA

Electrical data	
Short circuit protection	Yes
Reverse polarity protection	Yes
Mechanical data	
Type	Cylindrical threaded
Material (sensing face)	PBT
Housing material	Brass nickel plated
Dimension	12 mm
Housing length	40,4 mm
Connection types	Connector M12
Tightening torque max.	15 Nm (Front: 10 Nm)
Ambient conditions	
Operating temperature	-25 … +75 °C
Protection class	IP 67

2021-04-28 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.


Inductive proximity switch

IFRM 12P3703/S14L


Inductive proximity switch - standard

Article number: 10229703

Dimension drawing



Connection diagram



2021-04-28 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.