

Cable transducer

Interface SSI

Measuring length absolute up to 2.3 m

BMMS K23 SSI - MAGRES



BMMS K23 SSI with flange connector M12

Technical data - electrical ratings

Voltage supply	10...30 VDC
Consumption w/o load	≤60 mA (24 VDC)
Initializing time	≤170 ms after power on
Interface	SSI
Function	Linear position feedback
Resolution	0.0585 mm/step
Linearity	±0.13 % full scale output (f.s.o.)
Absolute accuracy	±0.26 % f.s.o. (+25 °C) ±0.34 % f.s.o. (-40...+85 °C)
Sensing method	Magnetic
Code	Gray or binary
Inputs	SSI clock Zero setting input
Output stages	SSI data: Linedriver RS422
Interference immunity	DIN EN 61000-6-2
Emitted interference	DIN EN 61000-6-4

Features

- Magnetic sensing method
- Resolution: 0.0585 mm/step
- Interface SSI
- Measuring length up to 2.3 m
- Removable stickers for water outlet
- Extremely light thanks to housing of plastic and aluminum

Technical data - mechanical design

Protection DIN EN 60529	IP 65 (encoder)
Materials	Encoder housing: aluminium Cable-pull housing: PA6 GF30 Cable: Stainless steel cable coated with polyamide
Operating temperature	-40...+85 °C
Service life	Typ. >500000 strokes
Measuring length	2.3 m
Distance/revolution	239.7 ±0.3 mm
Cable acceleration	≤50 m/s ²
Cable diameter	0.45 mm
Pull-in force	>3 N
Pull-out force	≤9 N
Relative humidity	95 % temporary condensing
Resistance	DIN EN 60068-2-6 Vibration 10 g, 10-2000 Hz DIN EN 60068-2-27 Shock 50 g, 11 ms
Weight approx.	400 g
Connection	Flange connector M12, 8-pin Cable 2 m
Bending radius	Cable: >55 mm
Special characteristics	Coated electronic
Instruction	Please consider the assembly instructions

Cable transducer

Interface SSI

Measuring length absolute up to 2.3 m

BMMS K23 SSI - MAGRES

Part number

BMMS K235

	24C	12/13	00		.	H	1
--	-----	-------	----	--	---	---	---

Measuring wire fixation
H Mount with hook

Connection
5 Cable 2 m, radial
N Flange connector M12, 8-pin, radial

Resolution
12/13 12/13 bit single-/multiturn

Voltage supply / signals
24C 10...30 VDC / SSI

Code
G Gray code
N Binary code

Accessories

Connectors and cables

10146775 Female connector M12, 8-pin, straight,
without cable

Cable transducer

Interface SSI

Measuring length absolute up to 2.3 m

BMMS K23 SSI - MAGRES

Terminal significance

+Vs	Encoder supply voltage.
0 V	Encoder ground connection relating to +Vs.
Data+	Positive data output.
Data-	Negative data output.
Clock+	Positive SSI clock input.
Clock-	Negative SSI clock input.
Zero	Input for setting a zero point anywhere within the encoder resolution. The zero setting operation is triggered by a Low impulse. Connect to +Vs after setting operation for maximum interference immunity. Impulse duration >2 ms.
Note	Include termination resistor R=120 Ohm between Data+ and Data- on control side.


Terminal assignment

Cable and flange connector M12
for connection references **-5** and **-N**

Pin	Core colour	Signals	Description
1	white	0 V	Supply voltage
2	brown	+Vs	Supply voltage
3	green	Clock+	Clock signal
4	yellow	Clock-	Clock signal
5	grey	Data+	Data signal
6	pink	Data-	Data signal
7	blue	Zero	Zero setting input
8	red	d.u.	do not use

Screen: connected to housing


Cable data: 8 x 0.14 mm²



Trigger level

Control inputs	Input circuit
Input level Low	<0,4 V (>2 ms)
Input level High	+Vs or open

Data transfer



$T = 1 \dots 10 \mu\text{s}$ $t_1 = 0.5 \dots 5 \mu\text{s}$

$t_2 \leq 12 \dots 26 \mu\text{s}$ $f \text{ max. } 1 \text{ MHz}$

Cable transducer


Interface SSI

Measuring length absolute up to 2.3 m

BMMS K23 SSI - MAGRES

Dimensions

BMMS K23 with cable radial



BMMS K23 with flange connector M12

