

IFRM 18P17A5/S14L

Inductive proximity switch - standard

Article number: 11078673

Overview

- 8 mm
- PNP make function (NO)
- connector M12
- -25 ... 75 °C
- IP 67



Picture similar







Technical data	
General data	
Mounting type	Quasi-flush
Nominal sensing distance Sn	8 mm
Hysteresis	3 20 % of Sr
Output indicator	LED red
Electrical data	
Switching frequency	< 500 Hz
Voltage supply range +Vs	6 36 VDC
Current consumption max. (no load)	10 mA
Output circuit	PNP make function (NO)
Voltage drop Vd	< 2 VDC
Output current	< 200 mA

Electrical data	
Short circuit protection	Yes
Reverse polarity protection	Yes
Mechanical data	
Туре	Cylindrical threaded
Material (sensing face)	PBT
Housing material	Brass nickel plated
Dimension	18 mm
Housing length	45 mm
Connection types	Connector M12
Tightening torque max.	40 Nm
Ambient conditions	
Operating temperature	-25 +75 °C
Protection class	IP 67

Remarks


Not for flush mounting in mild steel



IFRM 18P17A5/S14L

Inductive proximity switch - standard Article number: 11078673

Dimension drawing



Connection diagram

