Baumer
Passion for Sensors

Industrial cameras / CX series

VCXG-02M

Gigabit Ethernet, 0,3 Megapixel, Monochrome

Article number: 11165842

Overview

- 640 x 480 px
- ON Semiconductor PYTHON300
- 1/4" CMOS
- 403 fps
- Gigabit Ethernet
- available



Technical data

Sensor information	
Sensor	ON Semiconductor PYTHON300
Mono/Color	Mono
Sensor type	1/4″ CMOS
Shutter type	Global shutter
Resolution	640 × 480 px
Pixel size	4.8 × 4.8 µm
Exposure time	0,02 … 1000 ms
Acquisition formats	
Image formats, interface frame rate max.	Full Frame, 640 × 480 px, max. 403 fps Binning 2×2, 320 × 240 px, max. 595 fps Binning 2×1, 320 × 480 px, max. 595 fps Binning 1×2, 640 × 240 px, max. 595 fps
Image formats, aquisition frame rate max. (Burst Mode)	Full Frame, 640 × 480 px, max. 573 fps
Pixel formats	Mono8 Mono10
Image preprocessing	
Analog controls	Gain (0 … 12 dB) Offset (0 … 63 LSB 10 Bit)
Color models	Mono

Camera features	
Basic Functions	Exposure Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	Exposure Auto Gain Auto
Image Pre-processing	Image Flipping (X/Y) LUT / Gamma
Acquisition / Interface	Burst Mode Adjustable Framerate Device Link Throughput Limit Internal Image Buffer
Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 … 2 sec, tracking and buffering of up to 256 trigger signals

2021-05-05 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.

VCXG-02M

Gigabit Ethernet, 0,3 Megapixel, Monochrome


Article number: 11165842

Technical data

Camera features	
Process Synchronization	Events Timer Trigger Delay Debouncer Counter Sequencer Trigger via Action CMD (GigE) Additional Output Modes (e.g. Trigger Ready) Chunk data inside transferred image Encoder support via Counter End trigger source
Additional Functions	User Set Integrated temperature sensor Readable additional information (e.g. sensor information) Save Custom Data
Internal image buffer	15 MB 16 images (Trigger Mode) 1 image (Free Running Mode)
Interfaces and connectors	
Data interface	Gigabit Ethernet, Transfer rate 1000 Mbits/sec, Fast Ethernet, Transfer Rate 100 Mbits/sec, Connector: 8P8C Modular Jack (RJ45), screwable type
Process interface	M8 / 8 pins (SACC-DSI-M8MS-8CON-M8-L180)
Power supply	via M8 / 8 pins or Power over Ethernet (PoE)
Mechanical data	
Lens mount	C-mount

Mechanical data	
Width	29 mm
Height	29 mm
Depth	49 mm
Weight	≤ 120 g
Material	zinc die casting, baked varnish (until 02-2020 nickel-chrome-plated), IP 40
Electrical data	
Voltage supply range +Vs	12 … 24 V DC (external power supply) 36 … 57 V DC (Power over Ethernet)
Power consumption	approx. 2,4 W @ 12 VDC and 403 fps approx. 2,9 W @ 48 VDC (PoE) and 403 fps
Non-volatile memory	
Flash memory size	128 kB
Environmental conditions	
Operating temperature	0 … +65 ° @ T = measurement point
Humidity	10 … 90 % (non-condensing)
Protection class	IP 40
Digital I/Os	
Lines	1 input line 1 output line 2 general purpose lines
Conformity	
Conformity	CE RoHS KC (MISP-REI-BKR-VCXG-13M) EAC

Dimension drawing



2021-05-05 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.